

**CRIMP-SET PZ 50****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Crimp sets

**General ordering data**

Version	Assortment crimping tool, Crimping tool: PZ 50, Stripping tool: AM 25, Crimping range, min.: 25, Colour code: Weidmüller
Order No.	<a href="#">9028850000</a>
Type	CRIMP-SET PZ 50
GTIN (EAN)	403224838405 1
Qty.	1 pc(s).
Packaging	Plastic box

Creation date June 4, 2024 4:14:10 PM CEST

Catalogue status 01.06.2024 / We reserve the right to make technical changes.

**CRIMP-SET PZ 50****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Depth	261 mm	Depth (inches)	10.276 inch
Height	57 mm	Height (inches)	2.244 inch
Width	338 mm	Width (inches)	13.307 inch
Net weight	1,759.55 g		

**Technical data**

Description of article	Set includes crimping tool for up to 50 mm <sup>2</sup> , stripping tool and wire-end ferrules in Weidmüller colour code
------------------------	--

**Assortments**

Colour code	Weidmüller	Crimping range, max.	50 mm <sup>2</sup>
Crimping range, min.	25 mm <sup>2</sup>	Crimping tool	PZ 50
Number of AEH	200 pcs.	Packaging	Plastic box
Stripping tool	AM 25		

**Classifications**

ETIM 6.0	EC000524	ETIM 7.0	EC000524
ETIM 8.0	EC000524	ETIM 9.0	EC000524
ECLASS 9.0	27-40-02-18	ECLASS 9.1	27-40-02-18
ECLASS 10.0	27-40-02-18	ECLASS 11.0	27-40-02-18
ECLASS 12.0	27-40-02-18	ECLASS 13.0	27-40-02-18

**Environmental Product Compliance**

REACH SVHC	Lead 7439-92-1
SCIP	1eacbb3e-7931-4ebb-9179-f29fd9b50028

**Downloads**


Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	

**CRIMP-SET PZ 50****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****Conductor nom. cross-section 50mm<sup>2</sup>**

- supplied loose in poly-bag
- Weidmüller colour code
- DIN colour code

**General ordering data**

Type	H50,0/36D BL	Version		Packaging	
Order No.	<a href="#">9019340000</a>	Wire-end ferrule, Standard, 26 mm, 20 mm, blue		loose	
GTIN (EAN)	4008190067632				
Qty.	50 pc(s).				

**Tools**

Sheathing stripper for PVC cables

**General ordering data**


Type	AM 25	Version	
Order No.	<a href="#">9001540000</a>	Tools, Sheathing strippers	
GTIN (EAN)	4008190138271		
Qty.	1 pc(s).		

**CRIMP-SET PZ 50****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****Conductor nom. cross-section 35mm<sup>2</sup>**

- supplied loose in poly-bag
- Weidmüller colour code
- DIN colour code

**General ordering data**

Type	H35,0/30D 16 R	Version		Packaging	
Order No.	<a href="#">9019310000</a>	Wire-end ferrule, Standard, 19 mm, 16 mm, red		loose	
GTIN (EAN)	4008190102234				
Qty.	50 pc(s).				

**Crimping tools****Crimping tools for wire end ferrules, with and without plastic collars**

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation

**General ordering data**

Type	PZ 50	Version	
Order No.	<a href="#">9006450000</a>	Pressing tool, Crimping tool for wire-end ferrules, 25mm <sup>2</sup> , 50mm <sup>2</sup> ,	
GTIN (EAN)	4008190095796	Indent crimp	
Qty.	1 pc(s).		

## CRIMP-SET PZ 50

Weidmüller Interface GmbH &amp; Co. KG


Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

Conductor nom. cross-section 25mm<sup>2</sup>

- supplied loose in poly-bag
- Weidmüller colour code
- DIN colour code
- other colour code

## General ordering data

Type	H25,0/30T SW	Version	Packaging
Order No.	<a href="#">9021190000</a>	Wire-end ferrule, Standard, 18 mm, 16 mm, black	loose
GTIN (EAN)	4008190115166		
Qty.	50 pc(s).		
Type	H25,0/36T SW	Version	Packaging
Order No.	<a href="#">9021200000</a>	Wire-end ferrule, Standard, 24 mm, 22 mm, black	loose
GTIN (EAN)	4008190055400		
Qty.	50 pc(s).		