

**HTF DFF****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Crimping tools for for turned/stamped contact**

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation
- With stop for exact positioning of the contacts.

**General ordering data**

Version	Pressing tool, Crimping tool for contacts, 0.22mm², 2.5mm², B-Crimp
Order No.	<a href="#">9014140000</a>
Type	HTF DFF
GTIN (EAN)	4008190297305
Qty.	1 pc(s).

## HTF DFF

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Width	205 mm	Width (inches)	8.071 inch
Net weight	442 g		

## Technical data

Description of article	Crimping tools for Weidmüller DFF contacts	Version	Mechanical, without interchangeable inserts
------------------------	--	---------	---

## Description of contact

Conductor cross-section, max. AWG	AWG 14	Conductor cross-section, min. AWG	AWG 24
Crimping range, max.	2.5 mm <sup>2</sup>	Crimping range, min.	0.22 mm <sup>2</sup>
Type of contact	Weidmüller DFF		

## tool data crimping

Crimping type/profile	B-Crimp	Wire end ferrules cross-section, max.	2.5 mm <sup>2</sup>
Wire end ferrules cross-section, min.	0.22 mm <sup>2</sup>		

## Classifications

ETIM 6.0	EC000168	ETIM 7.0	EC000168
ETIM 8.0	EC000168	ETIM 9.0	EC000168
ECLASS 9.0	21-04-38-11	ECLASS 9.1	21-04-38-11
ECLASS 10.0	21-04-38-11	ECLASS 11.0	21-04-38-11
ECLASS 12.0	21-04-38-11	ECLASS 13.0	21-04-38-11

## Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	2159813b-98fd-4068-b62a-bc89a046c012
RoHS Compliance Status	Not affected

## Downloads

Approval/Certificate/Document of Conformity	<a href="#">Declaration of the Manufacturer</a>
Engineering Data	<a href="#">CAD data – STEP</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	

## HTF DFF

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

