

CRIMPFIX R**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

- For automatic stripping and crimping
- Time-saving and efficient processing
- Easily adjustable to the respective cross-section range
- Stripping and crimping in one work step
- The processing of sleeves or contacts from other manufacturers can cause machine failures and defects!

General ordering data

Version	Automatic stripper and crimper
Order No.	9028500000
Type	CRIMPFIX R
GTIN (EAN)	4008190860073
Qty.	1 pc(s).

CRIMPFIX R

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	330 mm	Depth (inches)	12.992 inch
Height	430 mm	Height (inches)	16.929 inch
Width	390 mm	Width (inches)	15.354 inch
Net weight	23,957 g		

PW65 maintenance - automatic stripping/crimping

Compressed-air connection	5 - 5.5 bar	Consumables	Linked wire-end ferrules
Crimping length	8 mm	Drive	Electropneumatic
Electrical connection	100-240 V / 50/60 Hz / 25 VA	Length of wire-end ferrule	14 mm
Pulse time	approx. 1 s	Stripping range	0.5 - 2.5 mm ² (~AWG 20-14)
Wire end ferrules cross-section, max.	2.5 mm ²	Wire end ferrules cross-section, min.	0.5 mm ²

Classifications

ETIM 6.0	EC002778	ETIM 7.0	EC002778
ETIM 8.0	EC002778	ETIM 9.0	EC002778
ECLASS 9.0	17-13-01-01	ECLASS 9.1	17-13-01-01
ECLASS 10.0	17-13-01-01	ECLASS 11.0	17-13-01-01
ECLASS 12.0	17-13-01-01	ECLASS 13.0	17-13-01-01

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	d2df479e-2b79-4e98-adc7-b03577df98ae

Approvals

Approvals



ROHS	Conform
------	---------

Downloads

User Documentation	Manual
Catalogues	Catalogues in PDF-format
Brochures	

CRIMPFIX R

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings



CRIMPFIX R

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Accessories / replacement parts



- For automatic stripping and crimping
- Time-saving and efficient processing
- Easily adjustable to the respective cross-section range
- Stripping and crimping in one work step
- The processing of sleeves or contacts from other manufacturers can cause machine failures and defects!

General ordering data

Type	FESA CF L/LS V2	Version
Order No.	1454790000	Automatic machines, Replacement part
GTIN (EAN)	4050118260779	
Qty.	1 pc(s).	
Type	FESA TPE CF UNI	Version
Order No.	1454800000	Automatic machines, Replacement part
GTIN (EAN)	4050118260687	
Qty.	1 pc(s).	
Type	HUELSENTRENNMESSER	Version
Order No.	1298740000	Accessories, Replacement part
GTIN (EAN)	4050118097108	
Qty.	1 pc(s).	
Type	CRIMPFIX MAGAZIN	Version
Order No.	2443370000	Accessories, Retaining clip
GTIN (EAN)	4050118457308	
Qty.	1 pc(s).	
Type	FESA CF L/LS V1	Version
Order No.	1454780000	Automatic machines, Replacement part
GTIN (EAN)	4050118260809	
Qty.	1 pc(s).	
Type	EXZ-SET CF L/LS V3	Version
Order No.	1484880000	Automatic machines, Replacement part
GTIN (EAN)	4050118293883	
Qty.	1 pc(s).	
Type	AIMESA CF U/L/LS SK TIN	Version
Order No.	1283530000	Automatic machines, Replacement part
GTIN (EAN)	4050118073676	
Qty.	1 pc(s).	
Type	SCHRSA CF L/LS V2	Version
Order No.	1454750000	Automatic machines, Replacement part
GTIN (EAN)	4050118260588	
Qty.	1 pc(s).	
Type	WTE CF L/LS V2/V3	Version
Order No.	1424470000	Automatic machines, Replacement part
GTIN (EAN)	4050118240276	
Qty.	1 pc(s).	
Type	SCHRSA CF L/LS V1	Version
Order No.	1454740000	Automatic machines, Replacement part
GTIN (EAN)	4050118260670	
Qty.	1 pc(s).	

Creation date May 23, 2024 7:37:13 AM CEST

Catalogue status 18.05.2024 / We reserve the right to make technical changes.

CRIMPFIX R**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories**

Type	AIMESA CF U/LS TIN	Version
Order No.	1132150000	Automatic machines, Replacement part
GTIN (EAN)	4032248920082	
Qty.	1 pc(s).	