


MULTI-STRIPAX AWG**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

- For flexible and solid conductors with special insulating materials
- High-quality stripping for industrial applications (complies with aircraft industry requirements)
- Specially shaped blades enable stripping of special types of insulation and conductor configurations
- Stripping length adjustable via end stop
- Very versatile thanks to interchangeable stripping units
- Stripping results reproduced accurately over and over again
- No damage to the conductor
- A long-lasting, reliable tool thanks to its sturdy design
- Integrated cutting function

General ordering data

Version	Tools, Stripping and cutting tool
Order No.	9202230000
Type	MULTI-STRIPAX AWG
GTIN (EAN)	4032248486168
Qty.	1 pc(s).

MULTI-STRIPAX AWG

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	40 mm	Depth (inches)	1.575 inch
Height	85 mm	Height (inches)	3.346 inch
Width	250 mm	Width (inches)	9.842 inch
Net weight	520.28 g		

Technical data

Description of article	Stripping and cutting tool for AWG conductors with PVC and PTFE etc. insulation
------------------------	---

Stripping tools

Cable type	AWG conductor with PTFE and PVC insulation	Conductor cross-section (cutting capacity)	6 mm ²
Conductor cross-section, max.	6 mm ²	Conductor cross-section, min.	0.12 mm ²
Copper cable - flexible, max.	6 mm ²	Stripping length, min.	2 mm
Stripping range AWG, max.	16 AWG	Stripping range AWG, min.	26 AWG
max. cutting capacity, fine-strand	6 mm ²	max. cutting capacity, ribbon	10,2 mm x 4 mm
max. cutting capacity, solid	2.5 mm ²		

Classifications

ETIM 6.0	EC002109	ETIM 7.0	EC002109
ETIM 8.0	EC002109	ETIM 9.0	EC002109
ECLASS 9.0	21-04-37-06	ECLASS 9.1	21-04-37-06
ECLASS 10.0	21-04-37-06	ECLASS 11.0	21-04-37-06
ECLASS 12.0	21-04-37-06	ECLASS 13.0	21-04-37-06

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	cf06c250-ed1e-4a45-9c1b-c5c8cbf13bf0

Downloads

User Documentation	Manual
Catalogues	Catalogues in PDF-format
Brochures	

MULTI-STRIPAX AWG

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Example of use

