

MULTI-STRIPAX 0.75-4 SL**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

- For flexible and solid conductors with special insulating materials
- High-quality stripping for industrial applications (complies with aircraft industry requirements)
- Specially shaped blades enable stripping of special types of insulation and conductor configurations
- Stripping length adjustable via end stop
- Very versatile thanks to interchangeable stripping units
- Stripping results reproduced accurately over and over again
- No damage to the conductor
- A long-lasting, reliable tool thanks to its sturdy design
- Integrated cutting function

General ordering data

Version	Tools, Stripping and cutting tool
Order No.	9203610000
Type	MULTI-STRIPAX 0.75-4 SL
GTIN (EAN)	4032248563968
Qty.	1 pc(s).

MULTI-STRIPAX 0.75-4 SL**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Depth	40 mm	Depth (inches)	1.575 inch
Height	85 mm	Height (inches)	3.346 inch
Width	250 mm	Width (inches)	9.842 inch
Net weight	519.28 g		

Technical data

Description of article	Stripping and cutting tool for cables with zero-halogen insulation, 0.75 - 4.0 mm ²
------------------------	--

Stripping tools

Cable type	Flexible and solid conductors with PVC insulation	Conductor cross-section (cutting capacity)	6 mm ²
Conductor cross-section, max.	4 mm ²	Conductor cross-section, min.	0.75 mm ²
Stripping length, min.	2 mm	max. cutting capacity, fine-strand	6 mm ²
max. cutting capacity, ribbon	10,2 mm x 4 mm	max. cutting capacity, solid	2.5 mm ²

Classifications

ETIM 6.0	EC002109	ETIM 7.0	EC002109
ETIM 8.0	EC002109	ETIM 9.0	EC002109
ECLASS 9.0	21-04-37-06	ECLASS 9.1	21-04-37-06
ECLASS 10.0	21-04-37-06	ECLASS 11.0	21-04-37-06
ECLASS 12.0	21-04-37-06	ECLASS 13.0	21-04-37-06

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	cf06c250-ed1e-4a45-9c1b-c5c8cbf13bf0

Downloads

User Documentation	Manual
Catalogues	Catalogues in PDF-format
Brochures	

MULTI-STRIPAX 0.75-4 SL

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Example of use



MULTI-STRIPAX 0.75-4 SL

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26


D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Accessories / replacement parts



- For flexible and solid conductors with special insulating materials
- High-quality stripping for industrial applications (complies with aircraft industry requirements)
- Specially shaped blades enable stripping of special types of insulation and conductor configurations
- Stripping length adjustable via end stop
- Very versatile thanks to interchangeable stripping units
- Stripping results reproduced accurately over and over again
- No damage to the conductor
- A long-lasting, reliable tool thanks to its sturdy design
- Integrated cutting function

General ordering data

Type	AIE MULTI-STRIPAX 6-16	Version
Order No.	9202260000	Insert
GTIN (EAN)	4032248486205	
Qty.	1 pc(s).	
Type	ERAN MULTI-STRIPAX	Version
Order No.	9203100000	Spare stop set
GTIN (EAN)	4032248538102	
Qty.	1 pc(s).	
Type	AIE MULTI-STRIPAX GKW/LW	Version
Order No.	9205770000	Insert
GTIN (EAN)	4032248836291	
Qty.	1 pc(s).	
Type	AIE M-SPX 0.25-1.5 S	Version
Order No.	9204550000	Insert
GTIN (EAN)	4032248671090	
Qty.	1 pc(s).	
Type	AIE M-SPX 1.5-6.0 S	Version
Order No.	9204570000	Insert
GTIN (EAN)	4032248671113	
Qty.	1 pc(s).	
Type	AIE MULTI-SPX 0.75-4 ² SL	Version
Order No.	9203730000	Insert
GTIN (EAN)	4032248576449	
Qty.	1 pc(s).	
Type	AIE MULTI-STRIPAX 16 SL	Version
Order No.	9202270000	Insert
GTIN (EAN)	4032248486212	
Qty.	1 pc(s).	
Type	ERME MULTI-STRIPAX	Version
Order No.	9203070000	Spare cutting blade
GTIN (EAN)	4032248538096	
Qty.	1 pc(s).	
Type	AIE MULTI-STRIPAX ASI	Version
Order No.	9202300000	Insert
GTIN (EAN)	4032248486250	
Qty.	1 pc(s).	

Creation date June 4, 2024 8:19:03 AM CEST

Catalogue status 01.06.2024 / We reserve the right to make technical changes.

MULTI-STRIPAX 0.75-4 SL**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories**

Type	AIE MULTI-STRIPAX POF	Version
Order No.	1212770000	Insert
GTIN (EAN)	4032248994434	
Qty.	1 pc(s).	
Type	AIE MULTI-STRIPAX AWG	Version
Order No.	9202280000	Insert
GTIN (EAN)	4032248486236	
Qty.	1 pc(s).	
Type	AIE MULTI-STRIPAX PV	Version
Order No.	1204280000	Insert
GTIN (EAN)	4032248987030	
Qty.	1 pc(s).	