

**QL 4 SAKK4****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Screwable cross-connections are easy to mount and de mount. Thanks to the big contact surface, even high currents can be transmitted with maximum contact reliability.

**General ordering data**

Version	Cross-connector (terminal), when screwed in, grey, 32 A, Number of poles: 4, Pitch in mm (P): 8.00, Insulated: No, Width: 29.7 mm
Order No.	<a href="#">9502560000</a>
Type	QL 4 SAKK4
GTIN (EAN)	4008190550554
Qty.	50 pc(s).

## QL 4 SAKK4

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	1 mm	Depth (inches)	0.039 inch
Height	6 mm	Height (inches)	0.236 inch
Width	29.7 mm	Width (inches)	1.169 inch
Net weight	1.14 g		

## Temperatures

Storage temperature	-25 °C...55 °C
---------------------	----------------

## Material data

Material	Copper	Colour	grey
----------	--------	--------	------

## System specifications

Version	Cross-connector
---------	-----------------

## Additional technical data

Explosion-tested version	No	Installation advice	Direct mounting
Type of fixing	when screwed in	Type of mounting	when screwed in

## Cross-connector

Number of cross-connected terminals	4	Rated current, multi-pole	32 A
Type	Cross-connector		

## Dimensions

Pitch in mm (P)	8 mm
-----------------	------

## General

Installation advice	Direct mounting	Number of poles	4
---------------------	-----------------	-----------------	---

## Rating data

Rated current	32 A
---------------	------

## Classifications

ETIM 6.0	EC000489	ETIM 7.0	EC000489
ETIM 8.0	EC000489	ETIM 9.0	EC000489
ECLASS 9.0	27-14-11-40	ECLASS 9.1	27-14-11-40
ECLASS 10.0	27-14-11-40	ECLASS 11.0	27-14-11-40
ECLASS 12.0	27-14-11-40	ECLASS 13.0	27-25-03-03

## Environmental Product Compliance

REACH SVHC	/
RoHS Compliance Status	Compliant without exemption

## QL 4 SAKK4

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Approvals

ROHS	Conform
------	---------

### Downloads

Engineering Data	<a href="#">CAD data – STEP</a>
User Documentation	<a href="#">StorageConditionsTerminalBlocks</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>