

**WQV 70N/3****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image****General ordering data**

Version	Cross-connector (terminal), when screwed in, Silver grey, 192 A, Number of poles: 3, Pitch in mm (P): 20.50, Insulated: No, Width: 9.5 mm
Order No.	<a href="#">9512250000</a>
Type	WQV 70N/3
GTIN (EAN)	4008190403935
Qty.	5 pc(s).

**WQV 70N/3****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Depth	18.6 mm	Depth (inches)	0.732 inch
Height	51 mm	Height (inches)	2.008 inch
Width	9.5 mm	Width (inches)	0.374 inch
Net weight	37.75 g		

**Temperatures**

Storage temperature	-25 °C...55 °C
---------------------	----------------

**Material data**

Material	tinned copper	Colour	Silver grey
----------	---------------	--------	-------------

**System specifications**

Version	For the terminals
---------	-------------------

**Additional technical data**

Type of fixing	when screwed in
----------------	-----------------

**Cross-connector**

Number of cross-connected terminals	3	Rated current, multi-pole	192 A
Type	Cross-connector		

**Dimensions**

Pitch in mm (P)	20.5 mm
-----------------	---------

**General**

Number of poles	3
-----------------	---

**Rating data**

Rated current	192 A
---------------	-------

**Classifications**

ETIM 6.0	EC000489	ETIM 7.0	EC000489
ETIM 8.0	EC000489	ETIM 9.0	EC000489
ECLASS 9.0	27-14-11-40	ECLASS 9.1	27-14-11-40
ECLASS 10.0	27-14-11-40	ECLASS 11.0	27-14-11-40
ECLASS 12.0	27-14-11-40	ECLASS 13.0	27-25-03-03

**Environmental Product Compliance**

REACH SVHC	/
RoHS Compliance Status	Compliant without exemption

**Approvals**

ROHS	Conform
------	---------

Creation date July 25, 2024 8:09:23 AM CEST

Catalogue status 13.07.2024 / We reserve the right to make technical changes.

## WQV 70N/3

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Downloads

Engineering Data	<a href="#">CAD data – 36042_WQV_70N-3_DXF.dxf</a> <a href="#">CAD data – STEP</a>
Engineering Data	<a href="#">Zuken E3.S</a>
User Documentation	<a href="#">StorageConditionsTerminalBlocks</a> <a href="#">Instruction</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	

**WQV 70N/3****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****Distance sleeve****General ordering data**

Type	VH 25.2/8/6.4	Version
Order No.	<a href="#">1967110000</a>	W-Series, Spacer sleeve
GTIN (EAN)	4032248739196	
Qty.	5 pc(s).	

**Cutting and notching tools for cross-connections**

- for Weidmüller Z-Series cross-connections
- for cross-connections from WQV 2.5 to WQV 35
- for cross-connection window of the terminal WSI 6

**General ordering data**

Type	WAW 1 NEUTRAL	Version
Order No.	<a href="#">9004500000</a>	Miscellaneous tools
GTIN (EAN)	4008190053925	
Qty.	1 pc(s).	