


**MP FPC 40/60****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Similar to illustration**

Mounting plates, 1.5 mm sheet steel, galvanised

**General ordering data**

Version	FPC (polycarbonate empty enclosure), Mounting plate, Mounting plate, Height: 360 mm, Width: 560 mm, Depth: 1.5 mm, Material: Sheet steel, galvanized, silver
Order No.	<a href="#">9535980000</a>
Type	MP FPC 40/60
GTIN (EAN)	4032248009695
Qty.	1 pc(s).

**MP FPC 40/60****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Depth	1.5 mm	Depth (inches)	0.059 inch
Height	360 mm	Height (inches)	14.173 inch
Width	560 mm	Width (inches)	22.047 inch
Net weight	2,316 g		

**General information**

Material	Sheet steel	Surface finish	galvanized
Type of fixing	when screwed in		

**Classifications**

ETIM 6.0	EC000213	ETIM 7.0	EC000213
ETIM 8.0	EC000213	ETIM 9.0	EC000213
ECLASS 9.0	27-40-06-39	ECLASS 9.1	27-18-92-90
ECLASS 10.0	27-40-06-39	ECLASS 11.0	27-40-06-39
ECLASS 12.0	27-40-06-39	ECLASS 13.0	27-40-06-39

**Environmental Product Compliance**

REACH SVHC	/
RoHS Compliance Status	Compliant without exemption

**Approvals**

ROHS	Conform
------	---------

**Downloads**

Engineering Data	<a href="#">CAD data – STEP</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	

**MP FPC 40/60****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****TS 35**

## Accessories

**General ordering data**

Type	TS35X7.5 ST FPC 40 VER	Version
Order No.	<a href="#">8000037562</a>	Rail, TS 35, TS 35 x 7.5, Width: 365 mm, with slot, without slot, Steel,
GTIN (EAN)	4050118653267	galvanized, chromium-plated
Qty.	20 pc(s).	
Type	TS35X7.5 ST FPC 60 HOR	Version
Order No.	<a href="#">8000037563</a>	Rail, TS 35, TS 35 x 7.5, Width: 565 mm, with slot, without slot, Steel,
GTIN (EAN)	4050118653274	galvanized, chromium-plated
Qty.	20 pc(s).	