

WK K PZ0**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Interchangeable bits for torque screwdriver**

Drive output acc. to DIN 5260-PZ, ISO 8764/1-PZ

General ordering data

Version	Screwdriver insert
Order No.	9918600000
Type	WK K PZ0
GTIN (EAN)	4032248388974
Qty.	1 pc(s).

WK K PZ0**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Depth	4 mm	Depth (inches)	0.157 inch
Height	4 mm	Height (inches)	0.157 inch
Width	175 mm	Width (inches)	6.89 inch
Net weight	25 g		

Technical data

Description of article	Interchangeable bit for crosshead screws, Pozidrive, size 0
------------------------	---

Screwing tools

Blade length	175 mm	Form	Pozidrive
Size	0	Torque setting, max.	0.9 Nm

Classifications

ETIM 6.0	EC002115	ETIM 7.0	EC002115
ETIM 8.0	EC003864	ETIM 9.0	EC003864
ECLASS 9.1	21-04-04-90	ECLASS 10.0	21-04-04-90
ECLASS 11.0	21-04-42-03	ECLASS 12.0	21-04-42-03
ECLASS 13.0	21-04-42-03		

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	6a3438d7-aa8c-48e4-8879-adf736ca79e3

Downloads

Catalogues	Catalogues in PDF-format
Brochures	

WK K PZO**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Torque screwdriver**

If you demand effective and exact work, it is essential to use the precise torque. This also guarantees high repetition accuracy.

This is the perfect job for the new Weidmüller torque screwdriver with the ergonomic grip and the unique interchangeable bit system.

- Compact and especially light design
- Torque set with special tool (supplied); an unintended, incorrect setting is ruled out.
- Ergonomic handle sizes matched to the torque range.
- Tools subjected to routine testing and provided with an ID number; 100% quality control with verification and product reference.
- Clicking sound upon reaching the set torque, clearly audible and noticeable, no unnecessary tightening.
- Interchangeable blades made from high-quality wear-resistant tool steel.
- All tools fulfil the accuracy requirements of: EN ISO 6798, BS EN 26789, ASME B107.14M
- Trigger accuracy +/- 6% of the set scale value.

General ordering data

Type	DMS MANUELL 2,0-7,0	Version
Order No.	9918380000	Torque screwdriver
GTIN (EAN)	4032248388349	
Qty.	1 pc(s).	

Type	DMS MANUELL 0,5-1,7	Version
Order No.	9918370000	Torque screwdriver
GTIN (EAN)	4032248388332	
Qty.	1 pc(s).	