

## SAIHG-M8B-M12-10

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Weidmüller is one of the industry's leading international providers of connectors. An important mainstay in this product family are the circular connectors, which Weidmüller groups under the product name SAI. In the development of SAI products, Weidmüller engineers have always concentrated on achieving rational, cost-effective installation concepts, and – in cooperation with major users – have supplied the markets with well-conceived products which set standards in terms of functionality and quality across the globe. The best examples are the new power distributors with S and T coded M12. These modules are characterised by particularly high currents and voltages. This enables them to also be used, for example, with three-phase motors.

## Általános rendelési adatok

Verzió	Beépített dugók, M8 aljzat, Szerelési magasság: 10 mm
Rendelési szám	<a href="#">2424500000</a>
Típus	SAIHG-M8B-M12-10
GTIN (EAN)	4050118432503
Qty.	25 Stück

## SAIHG-M8B-M12-10

Weidmüller Interface GmbH & Co. KG  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

## Műszaki adatok

## Méretetek és tömegek

Nettó tömeg	7,2 g
-------------	-------

## Dugaszoló NYÁK-csatlakozók műszaki adatai

Ház felülete	nikkelezett	Házak	M8 aljzat
Kódolás	nincs	Szerelési magasság	10 mm
Ház fő anyaga	CuZn	Csatlakozási menet	M8
Felerősítő menet	M 12	Tömítés anyaga	FPM, NBR

## Általános információk

Ház fő anyaga	CuZn	Csatlakozási menet	M8
---------------	------	--------------------	----

## Rendszerparaméterek

Érintkezősorok száma	1
----------------------	---

## Besorolások

ETIM 6.0	EC000437	ETIM 7.0	EC003556
ETIM 8.0	EC003556	ETIM 9.0	EC003556
ECLASS 9,1	27-44-02-02	ECLASS 10.0	27-44-02-24
ECLASS 11.0	27-44-02-24	ECLASS 12.0	27-44-02-24
ECLASS 13.0	27-44-02-24		

## Termékek környezetvédelmi megfelelése

REACH SVHC	Lead 7439-92-1
SCIP	Oea6d931-f9e9-40a6-89d9-8d67103189d3

## Tanúsítványok

ROHS	Megfelel
------	----------

## Letöltések


Engineering Data	<a href="#">CAD data – STEP</a>
Katalógusok	<a href="#">Catalogues in PDF-format</a>
Kiadványok	<a href="#">FL FIELDWIRING EN</a>

**SAIHG-M8B-M12-10****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Rajzok****Méretrajz**

## SAIHG-M8B-M12-10

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Tartozékok

## Tartozékok



Weidmüller is one of the industry's leading international providers of connectors. An important mainstay in this product family are the circular connectors, which Weidmüller groups under the product name SAI. In the development of SAI products, Weidmüller engineers have always concentrated on achieving rational, cost-effective installation concepts, and – in cooperation with major users – have supplied the markets with well-conceived products which set standards in terms of functionality and quality across the globe. The best examples are the new power distributors with S and T coded M12. These modules are characterised by particularly high currents and voltages. This enables them to also be used, for example, with three-phase motors.

## Általános rendelési adatok

Típus	SAIE-KMM12X1-SW14	Verzió
Rendelési szám	<a href="#">424570000</a>	Beépített dugók
GTIN (EAN)	4050118432473	
Qty.	25 Stück	