

QL 3 SAK35**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image**

Similar to illustration

Screwable cross-connections are easy to mount and de mount. Thanks to the big contact surface, even high currents can be transmitted with maximum contact reliability.

General ordering data

Version	Cross-connector (terminal), when screwed in, Number of poles: 3, Pitch in mm (P): 18.00, Insulated: No, 99 A, grey
Order No.	0123700000
Type	QL 3 SAK35
GTIN (EAN)	4008190182526
Qty.	20 pc(s).

QL 3 SAK35**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Depth	3 mm	Depth (inches)	0.118 inch
Height	8 mm	Height (inches)	0.315 inch
Width	45.8 mm	Width (inches)	1.803 inch
Net weight	8.05 g		

Temperatures

Storage temperature	-25 °C...55 °C
---------------------	----------------

Material data

Material	Cu Zn	Colour	grey
----------	-------	--------	------

System specifications

Version	Cross-connector
---------	-----------------

Additional technical data

Explosion-tested version	No	Installation advice	Direct mounting
Type of fixing	when screwed in	Type of mounting	when screwed in

Cross-connector

Number of cross-connected terminals	3	Rated current, 2-pole	110 A
Rated current, multi-pole	99 A	Type	Cross-connector

Dimensions

Pitch in mm (P)	18 mm	TS 32 offset	30 mm
TS 35 offset	30 mm		

General

Installation advice	Direct mounting	Number of poles	3
---------------------	-----------------	-----------------	---

Rating data

Rated current	99 A
---------------	------

Classifications

ETIM 6.0	EC000489	ETIM 7.0	EC000489
ETIM 8.0	EC000489	ETIM 9.0	EC000489
ECLASS 9.0	27-14-11-40	ECLASS 9.1	27-14-11-40
ECLASS 10.0	27-14-11-40	ECLASS 11.0	27-14-11-40
ECLASS 12.0	27-14-11-40	ECLASS 13.0	27-25-03-03

Approvals

ROHS	Conform
------	---------

QL 3 SAK35

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Downloads

Engineering Data	CAD data – STEP
User Documentation	StorageConditionsTerminalBlocks
Catalogues	Catalogues in PDF-format

QL 3 SAK35**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Miscellaneous**

We offer a broad portfolio of mounting support for easy handling and supplementation of our products. From various tools to insulating sleeves and various screws, our components are matched to each other down to the last detail and thus facilitate assembly in compliance with the respective standards and protective regulations.

General ordering data

Type	SS M4 D 128-A 4	Version
Order No.	0136400000	Lock washer, Copper
GTIN (EAN)	4008190118143	
Qty.	100 pc(s).	

Screws

Depending on the terminal block or also accessories, we offer different types of screws as additional items or also spare parts.

General ordering data

Type	BFSC M4X30	Version
Order No.	0267100000	Mounting screw (Terminal)
GTIN (EAN)	4008190187897	
Qty.	50 pc(s).	

QL 3 SAK35**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Connection sleeves****General ordering data**

Type	VH 17/8.2/5.2	Version
Order No.	0267000000	Connecting sleeve (terminal), Height: 8 mm, Width: 8 mm, Depth: 17
GTIN (EAN)	4008190146986	mm, Cu Zn
Qty.	50 pc(s).	