

STB 28.5 IH/SW SAK2.5**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image****STB 25 IH/6N 027120**

Similar to illustration

Test adapters and test plugs are used for the electrical connection between terminal blocks and the test equipment. In this way, an electrical contact can be established in the wired state and measurements can be done easily.

General ordering data

| | |
|------------|---|
| Version | Socket (terminal), Plug-in depth: 10 mm, Depth: 29.7 mm |
| Order No. | 0133400000 |
| Type | STB 28.5 IH/SW SAK2.5 |
| GTIN (EAN) | 4008190136567 |
| Qty. | 50 pc(s). |

STB 28.5 IH/SW SAK2.5**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

| | | | |
|------------|---------|----------------|------------|
| Depth | 29.7 mm | Depth (inches) | 1.169 inch |
| Net weight | 2.46 g | | |

Temperatures

| | |
|---------------------|----------------|
| Storage temperature | -25 °C...55 °C |
|---------------------|----------------|

Material data

| | |
|--------|-------|
| Colour | black |
|--------|-------|

System specifications

| | |
|---------|------------------------|
| Version | For the mounting rails |
|---------|------------------------|

Additional technical data

| | | | |
|--------------------------|-----------------|---------------------|-----------------|
| Explosion-tested version | No | Installation advice | Direct mounting |
| Type of fixing | when screwed in | Type of mounting | when screwed in |

Dimensions

| | |
|---------------|-------|
| Plug-in depth | 10 mm |
|---------------|-------|

General

| | |
|---------------------|-----------------|
| Installation advice | Direct mounting |
|---------------------|-----------------|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC002848 | ETIM 7.0 | EC002848 |
| ETIM 8.0 | EC002848 | ETIM 9.0 | EC002848 |
| ECLASS 9.0 | 27-14-11-92 | ECLASS 9.1 | 27-14-11-92 |
| ECLASS 10.0 | 27-14-11-92 | ECLASS 11.0 | 27-14-11-92 |
| ECLASS 12.0 | 27-14-11-92 | ECLASS 13.0 | 27-25-03-90 |

Environmental Product Compliance

| | |
|------------|--------------------------------------|
| REACH SVHC | Lead 7439-92-1 |
| SCIP | dce63e23-eea1-4eaa-9071-1c98fc8fa2ea |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|--------------------|---|
| Engineering Data | CAD data – STEP |
| User Documentation | StorageConditionsTerminalBlocks |
| Catalogues | Catalogues in PDF-format |