

TS 15X5 2M/AL/BK**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image**

Aluminum has the second best electrical conductivity after copper. One advantage is low weight, another is outstanding corrosion protection.

General ordering data

Version	Terminal rail, without slot, Accessories, 15 x 5.5 x 2000 mm, Aluminium, untreated
Order No.	0134700000
Type	TS 15X5 2M/AL/BK
GTIN (EAN)	4008190129026
Qty.	2 m
Delivery status	This article will no longer be available in the future.
Available until	2022-03-31
Alternative product	0514200000

TS 15X5 2M/AL/BK

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	5.5 mm	Depth (inches)	0.217 inch
Height	15 mm	Height (inches)	0.591 inch
Width	2,000 mm	Width (inches)	78.74 inch
Net weight	57.5 g		

Mounting rail

Installation advice	Direct mounting
Length of the terminal rail	max. 2,000 mm
	min. 0 mm
	nominal 2,000 mm
Material	Aluminium
Permitted thermal current for PEN function, max.	76 A
Pre-punched mounting rail	No
Short circuit strength corresponds to E-Cu wire	16 mm ²
Short-time withstand current per second according to IEC 60947-7-2	1.92 kA
Slit gap	
Slit length	
Slit width	
Standards	DIN EN 60715
Surface finish	untreated
Thickness	1 mm

Classifications

ETIM 6.0	EC001285	ETIM 7.0	EC001285
ETIM 8.0	EC001285	ETIM 9.0	EC001285
ECLASS 9.0	27-40-06-02	ECLASS 9.1	27-40-06-02
ECLASS 10.0	27-40-06-02	ECLASS 11.0	27-40-06-02
ECLASS 12.0	27-40-06-02	ECLASS 13.0	27-40-06-02

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
Engineering Data	Zuken E3.S
User Documentation	StorageConditionsTerminalBlocks
Catalogues	Catalogues in PDF-format
Brochures	

TS 15X5 2M/AL/BK

Weidmüller Interface GmbH & Co. KG


Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Drawings



TS 15X5 2M/AL/BK**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****TS 15**
TS 15

Weidmüller's range of products includes end brackets that guarantee a permanent, reliable mounting on the terminal rail and prevent sliding. Versions with and without screws are available. The end brackets include marking options, also for group markers, and also a test plug holder.

General ordering data

Type	EW 15	Version
Order No.	0382860000	End bracket, Polyamide 66, beige, Rail: TS 15, Direct mounting
GTIN (EAN)	4008190187804	
Qty.	50 pc(s).	
Type	ZEW 15	Version
Order No.	7920340000	End bracket, Plastic, beige, Rail: TS 15, Direct mounting
GTIN (EAN)	4032248238910	
Qty.	20 pc(s).	
Type	EW 15/2	Version
Order No.	1071900000	End bracket, Plastic, dark beige, Rail: TS 15, Direct mounting
GTIN (EAN)	4008190462949	
Qty.	50 pc(s).	

Mounting support

We offer a broad portfolio of mounting support for easy handling and supplementation of our products. From various tools to insulating sleeves and various screws, our components are matched to each other down to the last detail and thus facilitate assembly in compliance with the respective standards and protective regulations.

General ordering data

Type	SO SH1	Version
Order No.	0401460000	Busbar support
GTIN (EAN)	4008190188092	
Qty.	20 pc(s).	

TS 15X5 2M/AL/BK**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Screws**

Depending on the terminal block or also accessories, we offer different types of screws as additional items or also spare parts.

General ordering data

Type	BFSC M4X6 MS	Version
Order No.	0136300000	Mounting screw (Terminal)
GTIN (EAN)	4008190177713	
Qty.	50 pc(s).	
Type	BFSC M4X6	Version
Order No.	0149700000	Mounting screw (Terminal)
GTIN (EAN)	4008190016098	
Qty.	100 pc(s).	