

G 25/10.0A/M RT**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image**

For protection against overcurrent, we offer cartridge fuse with dimensions 5x25 mm in sizes from 250 mA to 6.3 A.

General ordering data

| | |
|------------|---|
| Version | Miniature fuse, medium time-lag, 10 A, G-Si. 5 x 25 |
| Order No. | 0193100000 |
| Type | G 25/10.0A/M RT |
| GTIN (EAN) | 4008190023799 |
| Qty. | 10 pc(s). |

G 25/10.0A/M RT**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

| | | | |
|------------|-------|-----------------|------------|
| Depth | 5 mm | Depth (inches) | 0.197 inch |
| Height | 25 mm | Height (inches) | 0.984 inch |
| Width | 5 mm | Width (inches) | 0.197 inch |
| Net weight | 1.3 g | | |

Material data

| | |
|--------|------------|
| Colour | Light Grey |
|--------|------------|

System specifications

| | |
|---------|------------------|
| Version | Fuse accessories |
|---------|------------------|

Fuse cartridges

| | | | |
|--------------------------|--------------|-------------------------|------------------|
| Cartridge fuse | G-Si. 5 x 25 | Characteristics | medium time-lag |
| Colour | Light Grey | Colour of the indicator | red |
| Current | 10 A | Melting integral | 370 A²s |
| Optical function display | Yes | Power output (@ 1.5 In) | 3.2 W |
| Rated breaking capacity | 1.5 kA | Version | Fuse accessories |
| Voltage drop | 150 mV | | |

Rating data

| | | | |
|---------------|-------|---------------|------|
| Rated voltage | 250 V | Rated current | 10 A |
|---------------|-------|---------------|------|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC000035 | ETIM 7.0 | EC000035 |
| ETIM 8.0 | EC002704 | ETIM 9.0 | EC002704 |
| ECLASS 9.0 | 27-14-20-01 | ECLASS 9.1 | 27-14-20-01 |
| ECLASS 10.0 | 27-14-20-01 | ECLASS 11.0 | 27-14-20-01 |
| ECLASS 12.0 | 27-14-20-01 | ECLASS 13.0 | 27-14-20-01 |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|--------------------|---|
| User Documentation | StorageConditionsTerminalBlocks |
| Catalogues | Catalogues in PDF-format |
| Brochures | |