


AP ST5**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

End plates are fitted to the open side of the last modular terminal before the end bracket. The use of an end plate ensures the function of the modular terminal and the specified rated voltage. It guarantees protection against contact with live parts and makes the final terminal finger-proof.

General ordering data

| | |
|------------|--|
| Version | End plate (terminals), 52 mm x 1.5 mm, beige |
| Order No. | 0447260000 |
| Type | AP ST5 |
| GTIN (EAN) | 4032248183913 |
| Qty. | 10 pc(s). |

AP ST5**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

| | | | |
|------------|---------|-----------------|------------|
| Depth | 30.3 mm | Depth (inches) | 1.193 inch |
| Height | 52 mm | Height (inches) | 2.047 inch |
| Width | 1.5 mm | Width (inches) | 0.059 inch |
| Net weight | 2.7 g | | |

Temperatures

| | | | |
|----------------------------------|----------------|----------------------------------|--------|
| Storage temperature | -25 °C...55 °C | Continuous operating temp., min. | -50 °C |
| Continuous operating temp., max. | 100 °C | | |

Material data

| | | | |
|---------------------------|-------|--------|-------|
| Material | PA 66 | Colour | beige |
| UL 94 flammability rating | V-2 | | |

System specifications

| | |
|---------|-----------|
| Version | End plate |
|---------|-----------|

Additional technical data

| | |
|---------------------|-----------------|
| Installation advice | Direct mounting |
|---------------------|-----------------|

General

| | |
|---------------------|-----------------|
| Installation advice | Direct mounting |
|---------------------|-----------------|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC000886 | ETIM 7.0 | EC000886 |
| ETIM 8.0 | EC000886 | ETIM 9.0 | EC000886 |
| ECLASS 9.1 | 27-14-11-33 | ECLASS 10.0 | 27-14-11-33 |
| ECLASS 11.0 | 27-14-11-33 | ECLASS 12.0 | 27-14-11-33 |
| ECLASS 13.0 | 27-25-03-01 | | |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|--------------------|---|
| Engineering Data | CAD data – STEP |
| User Documentation | StorageConditionsTerminalBlocks |
| Catalogues | Catalogues in PDF-format |