

AD 250**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image**

Protective covers or protective caps are attached to the respective connection area of the terminal blocks. They provide protection against electric shock caused by accidental contact with live parts due to operation or faults.

General ordering data

| | |
|------------|---|
| Version | Terminal cover, Transparent, Height: 70 mm, Width: 4 mm, Depth: 49.5 mm |
| Order No. | 0634100000 |
| Type | AD 250 |
| GTIN (EAN) | 4008190083199 |
| Qty. | 10 pc(s). |

AD 250

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|------------|---------|-----------------|------------|
| Depth | 49.5 mm | Depth (inches) | 1.949 inch |
| Height | 70 mm | Height (inches) | 2.756 inch |
| Width | 4 mm | Width (inches) | 0.157 inch |
| Net weight | 75.2 g | | |

Temperatures

| | | | |
|----------------------------------|----------------|----------------------------------|--------|
| Storage temperature | -25 °C...55 °C | Continuous operating temp., min. | -50 °C |
| Continuous operating temp., max. | 100 °C | | |

Material data

| | | | |
|--------|-------------|---------------------------|-----|
| Colour | Transparent | UL 94 flammability rating | V-2 |
|--------|-------------|---------------------------|-----|

System specifications

| | |
|---------|----------------------------|
| Version | End and intermediate plate |
|---------|----------------------------|

Additional technical data

| | | | |
|---------------------|-----------------|---------|----|
| Installation advice | Direct mounting | Snap-on | No |
|---------------------|-----------------|---------|----|

Dimensions

| | | | |
|--------------|-------|--------------|-------|
| TS 32 offset | 35 mm | TS 35 offset | 35 mm |
|--------------|-------|--------------|-------|

General

| | |
|---------------------|-----------------|
| Installation advice | Direct mounting |
|---------------------|-----------------|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC002848 | ETIM 7.0 | EC002848 |
| ETIM 8.0 | EC002848 | ETIM 9.0 | EC002848 |
| ECLASS 9.0 | 27-14-11-92 | ECLASS 9.1 | 27-14-11-92 |
| ECLASS 10.0 | 27-14-11-92 | ECLASS 11.0 | 27-14-11-92 |
| ECLASS 12.0 | 27-14-11-92 | ECLASS 13.0 | 27-25-03-90 |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|--------------------|---|
| User Documentation | StorageConditionsTerminalBlocks |
| Catalogues | Catalogues in PDF-format |