

HDC KIT HE-P 06.11 M**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

HDC kits are standardized kits for assembling complete plug-in connectors.

The HDC kits normally consist of a male insert, a female insert, a plug housing, a bulkhead housing and a cable gland.

Weidmüller offers a range of standard connector combinations with metric or PG cable entry threads.

The PUSH IN connection is a direct-insert method of connection. The preprocessed wire can be inserted directly into the wire connection without the need for any tools.

PUSH IN technology

General ordering data

Version	RockStar® HDC kits-Heavy-duty connectors, Kit, HE, Size: 3, Poles: 6, PUSH IN, 500 V, 24 A, diecast aluminium, M 20
Order No.	1061720000
Type	HDC KIT HE-P 06.11 M
GTIN (EAN)	4032248816446
Qty.	1 pc(s).

HDC KIT HE-P 06.11 M

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Net weight	384 g
------------	-------

Temperatures

Limit temperature	-40 °C ... 100 °C
-------------------	-------------------

General data

BG	3	Cable glands	M 20
Connection type PE	Screw connection	Material	diecast aluminium
Number of poles	6	Rated current (DIN EN 61884)	24 A
Rated voltage (DIN EN 61884)	500 V	Series	HE
Size	3		

Version

BG	3	Conductor cross-section, max.	4 mm ²
Conductor cross-section, min.	0.5 mm ²	Material	diecast aluminium
Size	3	Surface finish	Powder coating
Type of connection	PUSH IN		

Classifications

ETIM 6.0	EC002943	ETIM 7.0	EC002943
ETIM 8.0	EC002943	ETIM 9.0	EC002943
ECLASS 9.0	27-44-02-92	ECLASS 9.1	27-44-01-90
ECLASS 10.0	27-44-02-92	ECLASS 11.0	27-44-02-92
ECLASS 12.0	27-44-02-92	ECLASS 13.0	27-44-02-92

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1 Potassium perfluorobutane sulfonate 29420-49-3
SCIP	bfb1c983-6f18-4ba4-8907-38aad6aee076

Approvals

ROHS	Conform
------	---------

Downloads

Approval/Certificate/Document of Conformity	Manufacturer's declaration
Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format
Brochures	FL FIELDWIRING EN FL FIELDWIRING EN

HDC KIT HE-P 06.11 M**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****HDC COS**

Various accessories are available for our inserts. This includes coding elements for the inserts.

**General ordering data**

Type	HDC COS 32	Version
Order No.	1430800000	Heavy-duty connectors, Accessories, Coding System
GTIN (EAN)	4008190176181	
Qty.	1 pc(s).	

Type	HDC COS 24	Version
Order No.	1430900000	Heavy-duty connectors, Accessories, Coding System
GTIN (EAN)	4008190077228	
Qty.	1 pc(s).	

Type	HDC COS 16	Version
Order No.	1431000000	Heavy-duty connectors, Accessories, Coding System
GTIN (EAN)	4008190052706	
Qty.	1 pc(s).	

SPB

Various accessories are available for our inserts. This includes coding elements for the inserts.

**General ordering data**

Type	SPB-M 3	Version
Order No.	1203600000	Heavy-duty connectors, Accessories, Lock bolts
GTIN (EAN)	4008190120047	
Qty.	100 pc(s).	