

**WQV 16-4/6****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image**

Reducing cross-connectors enable simple and fast connection of terminal blocks with different rated cross-sections.

**General ordering data**

Version	Cross-connector (terminal), when screwed in, Number of poles: 2, Pitch in mm (P): 11.90, Insulated: Yes, 76 A, yellow
Order No.	<a href="#">1064000000</a>
Type	WQV 16-4/6
GTIN (EAN)	4008190173067
Qty.	10 pc(s).

## WQV 16-4/6

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	41.5 mm	Depth (inches)	1.634 inch
Height	18.75 mm	Height (inches)	0.738 inch
Width	13 mm	Width (inches)	0.512 inch
Net weight	11.877 g		

## Temperatures

Storage temperature	-25 °C...55 °C	Continuous operating temp., min.	-60 °C
Continuous operating temp., max.	130 °C		

## Material data

Material	PA 66	Colour	yellow
UL 94 flammability rating	V-0		

## System specifications

Version	For the terminals
---------	-------------------

## Additional technical data

Installation advice	Direct mounting	Type of fixing	when screwed in
---------------------	-----------------	----------------	-----------------

## Cross-connector

Number of cross-connected terminals	2	Rated current, 2-pole	41 A
Rated current, multi-pole	32 A	Tightening torque range for fixing screw	0.4...0.8 Nm
Type	Cross-connector		

## Dimensions

Pitch in mm (P)	11.9 mm
-----------------	---------

## General

Installation advice	Direct mounting	Number of poles	2
---------------------	-----------------	-----------------	---

## Rating data

Rated current	76 A
---------------	------

## Classifications

ETIM 6.0	EC000489	ETIM 7.0	EC000489
ETIM 8.0	EC000489	ETIM 9.0	EC000489
ECLASS 9.0	27-14-11-40	ECLASS 9.1	27-14-11-40
ECLASS 10.0	27-14-11-40	ECLASS 11.0	27-14-11-40
ECLASS 12.0	27-14-11-40	ECLASS 13.0	27-25-03-03

## Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	3431e478-7f08-4004-abeb-15560ca39d73

**WQV 16-4/6****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Approvals**

ROHS	Conform
------	---------

**Downloads**

Approval/Certificate/Document of Conformity	<a href="#">Confirmation of Standards EN 45545-2_2020-10</a>
---	--

Engineering Data	<a href="#">CAD data – STEP</a>
------------------	---------------------------------

Engineering Data	<a href="#">Zuken E3.S</a>
------------------	----------------------------

User Documentation	<a href="#">Beipackzettel_WQV16-2.5.pdf</a> <a href="#">StorageConditionsTerminalBlocks</a>
--------------------	--

Catalogues	<a href="#">Catalogues in PDF-format</a>
------------	--

## WQV 16-4/6

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

### Cutting and notching tools for cross-connections



- for Weidmüller Z-Series cross-connections
- for cross-connections from WQV 2.5 to WQV 35
- for cross-connection window of the terminal WSI 6

### General ordering data

Type	WAW 1 NEUTRAL	Version
Order No.	<a href="#">9004500000</a>	Miscellaneous tools
GTIN (EAN)	4008190053925	
Qty.	1 pc(s).	