

**Q 2 WDL2.5S****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image****Building installation wiring**

For building installations, we offer a complete system that revolves around the 10×3 copper rail and comprises perfectly coordinated components: from installation terminal blocks, neutral conductor terminal blocks and distribution terminal blocks to comprehensive accessories such as busbars and busbar holders.

**General ordering data**

Version	Cross-connector (terminal), when screwed in, Number of poles: 2, Pitch in mm (P): 6.10, Insulated: Yes, 24 A, yellow
Order No.	<a href="#">1071500000</a>
Type	Q 2 WDL2.5S
GTIN (EAN)	4008190424930
Qty.	50 pc(s).

**Q 2 WDL2.5S****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

Depth	9.5 mm	Depth (inches)	0.374 inch
Height	10.1 mm	Height (inches)	0.398 inch
Width	4 mm	Width (inches)	0.157 inch
Net weight	1.64 g		

**Temperatures**

Storage temperature	-25 °C...55 °C
---------------------	----------------

**Material data**

Material	tinned copper	Colour	yellow
----------	---------------	--------	--------

**System specifications**

Version	For the terminals
---------	-------------------

**Additional technical data**

Explosion-tested version	No	Installation advice	Feed-through (bushing), Direct mounting
Type of fixing	when screwed in		

**Dimensions**

Pitch in mm (P)	6.1 mm
-----------------	--------

**General**

Installation advice	Feed-through (bushing), Direct mounting	Number of poles	2
---------------------	---	-----------------	---

**Rating data**

Rated current	24 A
---------------	------

**Classifications**

ETIM 6.0	EC000489	ETIM 7.0	EC000489
ETIM 8.0	EC000489	ETIM 9.0	EC000489
ECLASS 9.0	27-14-11-40	ECLASS 9.1	27-14-11-40
ECLASS 10.0	27-14-11-40	ECLASS 11.0	27-14-11-40
ECLASS 12.0	27-14-11-40	ECLASS 13.0	27-25-03-03

**Environmental Product Compliance**

REACH SVHC	Lead 7439-92-1
SCIP	abe9d042-078a-4094-b143-0a6a4ced35a2

**Approvals**

ROHS	Conform
------	---------

## Q 2 WDL2.5S

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Downloads

Engineering Data	<a href="#">CAD data – STEP</a>
Engineering Data	<a href="#">Zuken E3.S</a>
User Documentation	<a href="#">StorageConditionsTerminalBlocks</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	