

SAI-M23-KSC-0.08/0.56**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

The M23 round plug-in connectors offer a high number of mating cycles, high current-carrying capacity and high contact-density coupled with minimum dimensions. Enclosures, inserts and crimp contacts need to be ordered separately.

General ordering data

Version	Sensor/Actuator plug-in connector, Crimp contact
Order No.	1170140000
Type	SAI-M23-KSC-0.08/0.56
GTIN (EAN)	4032248962235
Qty.	50 pc(s).

SAI-M23-KSC-0.08/0.56

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Net weight	0.26 g
------------	--------

Settings re. SAI M23 crimping tool

Settings regarding SAI M23 crimping tool	Locator position	11	
	Crimp contact	Crimp male 1 mm	
	Crimping Tool	1	
	Crimping mandrel adjustment acc. to mm ²	Wire cross-section	0.08 mm ²
		Crimping mandrel adjustment	0.78
		Wire cross-section	0.14 mm ²
		Crimping mandrel adjustment	0.81
	Locator position	1	
	Crimp contact	Crimp male 1 mm	
	Crimping Tool	2	
	Crimping mandrel adjustment acc. to mm ²	Wire cross-section	0.08 mm ²
		Crimping mandrel adjustment	0.72

Technical data customisable plug-in connectors

Conductor cross-section, max.	0.56 mm ²	Conductor cross-section, min.	0.08 mm ²
Contact material	Copper-Zinc alloy	Contact surface	Gold-plated
Insulation strength	> 10 ¹⁰ Ω	Plugging cycles	> 1000
Type of connection	Crimp connection		

Classifications

ETIM 6.0	EC000796	ETIM 7.0	EC000796
ETIM 8.0	EC000796	ETIM 9.0	EC000796
ECLASS 9.0	27-44-02-92	ECLASS 9.1	27-44-02-90
ECLASS 10.0	27-44-02-92	ECLASS 11.0	27-44-02-92
ECLASS 12.0	27-44-02-92	ECLASS 13.0	27-44-02-92

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	ebf89fc8-a87f-4691-b87a-dfb9921774b4

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (UR)	E344862

SAI-M23-KSC-0.08/0.56**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Downloads

Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format
Brochures	FL FIELDWIRING EN FL FIELDWIRING EN

SAI-M23-KSC-0.08/0.56

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Drawings

Drawing



SAI-M23-KSC-0.08/0.56**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****...for M23**

Weidmüller offers a wide range of tools and accessories for sensor-actuator cabling.

General ordering data

Type	SAI M23 CRIMPING TOOL 2	Version
Order No.	1203960000	Pressing tool for signal contacts
GTIN (EAN)	4050118000764	
Qty.	1 pc(s).	
Type	SAI M23 CRIMPING TOOL 1	Version
Order No.	1203840000	Pressing tool for signal and power contacts
GTIN (EAN)	4032248986934	
Qty.	1 pc(s).	