

**SKMUS M16-W****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

**General ordering data**

|            |   |
|------------|---|
| Version    | SKMU SS (stainless steel locknut), Locknut, M16, 2.2 mm, Stainless steel 1.4404 |
| Order No.  | <a href="#">1185680000</a>  |
| Type       | SKMUS M16-W   |
| GTIN (EAN) | 4050118269956   |
| Qty.       | 240 pc(s).  |

**SKMUS M16-W****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

|            |        |                 |            |
|------------|--------|-----------------|------------|
| Height     | 3.2 mm | Height (inches) | 0.126 inch |
| Net weight | 4 g    |                 |            |

**General information**

|                 |                        |                  |              |
|-----------------|------------------------|------------------|--------------|
| AF size 1       | 20 mm                  | Cable glands     | M 16         |
| External thread | M16                    | Halogen          | halogen-free |
| Internal thread | M 16                   | Length of thread | 2.2 mm       |
| Material        | Stainless steel 1.4404 | Pitch of thread  | 1.5 mm       |
| Thickness       | 2.8 mm                 |                  |              |

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC000940    | ETIM 7.0    | EC000940    |
| ETIM 8.0    | EC000940    | ETIM 9.0    | EC000940    |
| ECLASS 9.0  | 27-14-44-24 | ECLASS 9.1  | 27-14-44-24 |
| ECLASS 10.0 | 27-14-44-24 | ECLASS 11.0 | 27-14-44-24 |
| ECLASS 12.0 | 27-14-08-05 | ECLASS 13.0 | 27-14-08-05 |

**Approvals**

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

**Downloads**

|                  |  |
|------------------|--|
| Engineering Data | <a href="#">CAD data – STEP</a>          |
| Catalogues       | <a href="#">Catalogues in PDF-format</a> |