

**CLI R 1-12 RT TRIP****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Similar to illustration

The CableLine range of wire and cable marker products provides users with solutions for the most diverse applications. The range of applications extends from narrow wires right up to cables with large outside diameters.

**General ordering data**

|            |                             |
|------------|-----------------------------|
| Version    | CableLine, Mounting mandrel |
| Order No.  | <a href="#">1208940000</a>  |
| Type       | CLI R 1-12 RT TRIP          |
| GTIN (EAN) | 4032248990337               |
| Qty.       | 10 pc(s).                   |

**CLI R 1-12 RT TRIP****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

|            |       |
|------------|-------|
| Net weight | 1.9 g |
|------------|-------|

**Temperatures**

|                             |             |
|-----------------------------|-------------|
| Operating temperature range | -30...80 °C |
|-----------------------------|-------------|

**General data**

|                                   |                           |                                   |                            |
|-----------------------------------|---------------------------|-----------------------------------|----------------------------|
| Colour                            | To customer specification | Colour of printing                | black                      |
| Halogen                           | Yes                       | Material                          | PVC, soft, without Cadmium |
| Number per mandrel                | 5                         | Operating temperature range       | -30...80 °C                |
| Operating temperature range, max. | 80 °C                     | Operating temperature range, min. | -30 °C                     |
| Orientation of print              | horizontal                | Printed characters                | Mixed characters           |
| Printing method                   | hot-embossing             | Type of printing                  | To customer specification  |
| UL 94 flammability rating         | V-0                       | Version                           | MultiPack                  |

**Conductor and cable markers**

|                               |                     |                                  |                         |
|-------------------------------|---------------------|----------------------------------|-------------------------|
| Conductor O.D.                | 2.5 - 5 mm          | Conductor O.D., max.             | 5 mm                    |
| Conductor O.D., min.          | 2.5 mm              | Conductor cross-section, max.    | 4 mm <sup>2</sup>       |
| Conductor cross-section, min. | 1.5 mm <sup>2</sup> | Cross-section for connected wire | 1.5 - 4 mm <sup>2</sup> |
| Halogen                       | Yes                 |                                  |                         |

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC001530    | ETIM 7.0    | EC001530    |
| ETIM 8.0    | EC001530    | ETIM 9.0    | EC001530    |
| ECLASS 9.0  | 27-40-04-01 | ECLASS 9.1  | 27-40-06-29 |
| ECLASS 10.0 | 27-40-04-01 | ECLASS 11.0 | 27-28-11-02 |
| ECLASS 12.0 | 27-28-11-02 | ECLASS 13.0 | 27-28-11-02 |

**Approvals**

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

**Downloads**

|                             |  |
|-----------------------------|--|
| Product Change Notification | <a href="#">PCN CableLine_DE</a><br><a href="#">PCN CableLine_EN</a> |
| Catalogues                  | <a href="#">Catalogues in PDF-format</a>                             |