

EBR-MODULE RS232**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image****Module for saving and loading a device configuration**

- Reduced system downtime by simple reconfiguration if equipment is swapped over
- Automatic loading of the saved configuration possible after device restart
- Compact and robust design
- Useable with all Weidmüller managed switches and industrial WLAN devices

General ordering data

Version	Configuration module, IP40, 0 °C...60 °C
Order No.	1241430000
Type	EBR-MODULE RS232
GTIN (EAN)	4050118029086
Qty.	1 pc(s).

EBR-MODULE RS232

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	97 mm	Depth (inches)	3.819 inch
Height	12 mm	Height (inches)	0.472 inch
Width	32.5 mm	Width (inches)	1.28 inch
Net weight	50 g		

Temperatures

Storage temperature	-20 °C...70 °C	Operating temperature	0 °C...60 °C
Humidity	5 to 95 % (non-condensing)		

EMC conformity and approvals

EMC standards	FCC Part 15, CISPR (EN55022) Class A, EN 61000-4-2 (ESD), Stage 2, EN 61000-4-3 (RS), Stage 3, EN 61000-4-4 (EFT), Stage 3, EN 61000-4-5 (surge voltage), Stage 3, EN 61000-4-6 (CS), Stage 3
---------------	---

Environmental conditions

Humidity	5 to 95 % (non-condensing)	Operating temperature, max.	60 °C
Operating temperature, min.	0 °C	Storage temperature, max.	70 °C
Storage temperature, min.	-20 °C		

Guarantee

Time interval	5 years
---------------	---------

Power supply

Connection type	RJ45-Port, RS232
-----------------	------------------

Technical data

Cable length	0.35 m	Housing main material	PVC casting
Protection degree	IP40	Type of fixing	M4 screw (< 4 mm)

Classifications

ETIM 6.0	EC001068	ETIM 7.0	EC001068
ETIM 8.0	EC001068	ETIM 9.0	EC001068
ECLASS 9.1	19-15-07-90	ECLASS 10.0	19-15-07-90
ECLASS 11.0	19-17-03-04	ECLASS 12.0	19-17-03-04
ECLASS 13.0	19-17-03-04		

EBR-MODULE RS232**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Approvals**

Approvals



ROHS

Conform

DownloadsApproval/Certificate/Document of Conformity [UK Declaration of Conformity](#)
[EU Declaration of Conformity](#)Engineering Data [CAD data – STEP](#)User Documentation [Hardware Installation Guide](#)Catalogues [Catalogues in PDF-format](#)

Brochures