

**SDIK PH2 SL****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com) 1000 V  
IEC 60900

VDE insulated screwdriver sets, for working on live parts up to 1000 V AC and 1500 V DC, DIN EN 60900. IEC 900. Each piece is "GS" safety tested. Blade made from fully hardened, high-alloy chromium-vanadium-molybdenum steel, gun-metal finish.

**General ordering data**

Version	Screwdriver, Screwdriver
Order No.	<a href="#">1274720000</a>
Type	SDIK PH2 SL
GTIN (EAN)	4050118073232
Qty.	1 pc(s).
Delivery status	<b>This article will no longer be available in the future.</b>
Available until	2021-08-06
Alternative product	<a href="#">2749660000</a>

**SDIK PH2 SL****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Width	218 mm	Width (inches)	8.583 inch
Diameter	36 mm	Net weight	98 g

**Technical data**

Description of article	VDE-insulated crosshead screwdriver, Phillips size 2, SlimLine
------------------------	----------------------------------------------------------------

**Screwing tools**

Blade length	100 mm	Blade size, crosshead	Gr. PH2
Form	Crosshead	Size	2

**Classifications**

ETIM 6.0	EC000144	ETIM 7.0	EC000144
ETIM 8.0	EC000144	ETIM 9.0	EC000144
ECLASS 9.0	21-04-04-06	ECLASS 9.1	21-04-04-06
ECLASS 10.0	21-04-04-06	ECLASS 11.0	21-04-04-06
ECLASS 12.0	21-04-04-06	ECLASS 13.0	21-04-04-06

**Environmental Product Compliance**

REACH SVHC	Lead 7439-92-1
SCIP	b28ab223-64ec-44cf-adb0-4dd6ebcae141

**Downloads**

Approval/Certificate/Document of Conformity	<a href="#">Manufacturer's Declaration - Screwdrivers</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	

**SDIK PH2 SL**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

**Example of use**