

SCREWTY-SW13-DM**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**The ideal tool for any application**

Screwty® is the ideal, all-purpose tool for tightening all common sensor and actuator cables. Even difficult-to-reach round plugs are accessible using the Screwty®. A simple turning movement tightens and loosens the connectors without the need for excessive force. The Screwty® is a unique and global solution since it fits with most cables and plugs from other vendors (over 90 %). The Screwty® consists of a handle with a conventional 1/4" adapter. Thus it can be used for all sizes: for M12 and M8 round plug-in connectors, and for M12F and M8F customisable plugs and sockets, as well as for all M23 plugs and sockets.

General ordering data

Version	Bolting tool
Order No.	1389190000
Type	SCREWTY-SW13-DM
GTIN (EAN)	4050118189742
Qty.	1 pc(s).
Packaging	Cardboard box

SCREWTY-SW13-DM**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Net weight	226.26 g
------------	----------

Screwing tools

Torque setting, max.	1.7 Nm	Torque setting, min.	0.5 Nm
----------------------	--------	----------------------	--------

Classifications

ETIM 6.0	EC000149	ETIM 7.0	EC000149
ETIM 8.0	EC000149	ETIM 9.0	EC000149
ECLASS 9.0	21-04-50-03	ECLASS 9.1	21-01-90-90
ECLASS 10.0	21-04-50-03	ECLASS 11.0	21-01-90-90
ECLASS 12.0	21-01-90-90	ECLASS 13.0	21-01-90-90

Important note

Product information	Included in delivery: <ul style="list-style-type: none">• Torque screwdriver 0.5-1.7 Nm + Setting aid• Interchangeable blade AF13
---------------------	--

Downloads

Product Change Notification	20210319 Technical change to Screwty® torque screwdriver 20210319 Technische Änderung zu Screwty® Drehmomentschraubendreher
Catalogues	Catalogues in PDF-format
Brochures	FL FIELDWIRING EN

SCREWTY-SW13-DM

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Screwty® cable gland tool with torque function



The ideal tool for any application

Screwty® is the ideal, all-purpose tool for tightening all common sensor and actuator cables. Even difficult-to-reach round plugs are accessible using the Screwty®. A simple turning movement tightens and loosens the connectors without the need for excessive force. The Screwty® is a unique and global solution since it fits with most cables and plugs from other vendors (over 90 %). The Screwty® consists of a handle with a conventional 1/4" adapter. Thus it can be used for all sizes: for M12 and M8 round plug-in connectors, and for M12F and M8F customisable plugs and sockets, as well as for all M23 plugs and sockets.

General ordering data

Type	SCREWTY SW12	Version	Packaging
Order No.	2598970000	Interchangeable blade for cable gland tool	Cardboard box
GTIN (EAN)	4050118781151		
Qty.	1 pc(s).		
Type	SCREWTY SW9	Version	Packaging
Order No.	1254630000	Interchangeable blade for cable gland tool	Cardboard box
GTIN (EAN)	4050118054194		
Qty.	1 pc(s).		
Type	SCREWTY SW17	Version	Packaging
Order No.	1254660000	Interchangeable blade for cable gland tool	Cardboard box
GTIN (EAN)	4050118051841		
Qty.	1 pc(s).		
Type	SCREWTY SW18	Version	Packaging
Order No.	1254670000	Interchangeable blade for cable gland tool	Cardboard box
GTIN (EAN)	4050118051858		
Qty.	1 pc(s).		
Type	SCREWTY SW13	Version	Packaging
Order No.	1254650000	Interchangeable blade for cable gland tool	Cardboard box
GTIN (EAN)	4050118051834		
Qty.	1 pc(s).		
Type	SCREWTY SW19	Version	Packaging
Order No.	1254680000	Interchangeable blade for cable gland tool	Cardboard box
GTIN (EAN)	4050118048827		
Qty.	1 pc(s).		
Type	SCREWTY SW10	Version	Packaging
Order No.	1254640000	Interchangeable blade for cable gland tool	Cardboard box
GTIN (EAN)	4050118048599		
Qty.	1 pc(s).		
Type	SCREWTY SW15	Version	Packaging
Order No.	1290830000	Interchangeable blade for cable gland tool	Cardboard box
GTIN (EAN)	4050118084320		
Qty.	1 pc(s).		