

HDC HP 250 M CM3**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Crimps provide a electrical and mechanical connection between wire and contact that is both secure and reliable. The optimal crimp connection is gas-tight and corrosion-resistant.

General ordering data

Version	HDC insert, Pin, Crimp connection
Order No.	1415410000
Type	HDC HP 250 M CM3
GTIN (EAN)	4050118216370
Qty.	1 pc(s).

HDC HP 250 M CM3**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Net weight	41.21 g
------------	---------

General data

Colour	black	Free from halogens	false
Material	Copper alloy	Type	Pin
Type of connection	Crimp connection		

Version

Material	Copper alloy	Type of connection	Crimp connection
----------	--------------	--------------------	------------------

Classifications

ETIM 6.0	EC000796	ETIM 7.0	EC000796
ETIM 8.0	EC000796	ETIM 9.0	EC000796
ECLASS 9.0	27-44-02-04	ECLASS 9.1	27-44-02-04
ECLASS 10.0	27-44-02-04	ECLASS 11.0	27-44-02-04
ECLASS 12.0	27-44-02-04	ECLASS 13.0	27-44-02-04

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	6eabd5ae-2d6b-409e-8bdf-87c27ee10e40

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
User Documentation	1487780000_00_11_13_BPZ_HDC_HP250-550_web.pdf
Catalogues	Catalogues in PDF-format
Brochures	FL FIELDWIRING EN FL FIELDWIRING EN

HDC HP 250 M CM3

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Crimp contacts CM3



Crimps provide a electrical and mechanical connection between wire and contact that is both secure and reliable. The optimal crimp connection is gas-tight and corrosion-resistant.

General ordering data

Type	HDC-C-M3-SM1.5AG	Version
Order No.	1698120000	Heavy-duty connectors, Crimp contact, CM 3, Pin, Conductor cross-
GTIN (EAN)	4008190885038	section, max.: 1.5, turned, Copper alloy
Qty.	100 pc(s).	
Type	HDC-C-M3-SM6.0AG	Version
Order No.	1682280000	Heavy-duty connectors, Crimp contact, CM 3, Pin, Conductor cross-
GTIN (EAN)	4008190474010	section, max.: 6, turned, Copper alloy
Qty.	100 pc(s).	
Type	HDC-C-M3-SM4.0AG	Version
Order No.	1682260000	Heavy-duty connectors, Crimp contact, CM 3, Pin, Conductor cross-
GTIN (EAN)	4008190473990	section, max.: 4, turned, Copper alloy
Qty.	100 pc(s).	
Type	HDC-C-M3-SM10.0AG	Version
Order No.	1682300000	Heavy-duty connectors, Crimp contact, CM 3, Pin, Conductor cross-
GTIN (EAN)	4008190474034	section, max.: 10, turned, Copper alloy
Qty.	100 pc(s).	
Type	HDC-C-M3-SM2.5AG	Version
Order No.	1698140000	Heavy-duty connectors, Crimp contact, CM 3, Pin, Conductor cross-
GTIN (EAN)	4008190885052	section, max.: 2.5, turned, Copper alloy
Qty.	100 pc(s).	