

THM ET 200SP 12.8/31 GE**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

THM ET S7 non-adhesive, roll-packaged labels are used to label the SIMATIC ET 200S and S7-modules from Siemens.

The M-Print® PRO software can be used to individually print the THM ET S7 labels with a THM printer. Labels can be easily separated. The THM MultiMark printer ensures highly-resistant printing.

General ordering data

Version	THM, Device markers, 31 x 12.8 mm, Siemens, yellow
Order No.	1487690000
Type	THM ET 200SP 12.8/31 GE
GTIN (EAN)	4050118296518
Qty.	1 pc(s).
compatible printer	2599430000 2599440000

THM ET 200SP 12.8/31 GE**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Depth	0.08 mm	Depth (inches)	0.003 inch
Height	31 mm	Height (inches)	1.22 inch
Width	12.8 mm	Width (inches)	0.504 inch
Net weight	438 g		

Temperatures

Operating temperature range	-50...100 °C
-----------------------------	--------------

General data

Application/manufacture	Siemens	
Approval acc. to UL 969	No	
Colour	yellow	
Halogen	No	
Material	Polypropylene	
Number of markers per combination	1 Label reel = Device markers	
Number of markers per packaging unit	Form of supply	Label reel
Number per roll	2,000	
Operating temperature range	-50...100 °C	
Operating temperature range, max.	100 °C	
Operating temperature range, min.	-50 °C	
Printing method	Thermal transfer	
UL 94 flammability rating	HB	
Version	halogen-free	
Width	12.8 mm	

Device markers

Halogen	No
---------	----

Classifications

ETIM 6.0	EC001288	ETIM 7.0	EC001288
ETIM 8.0	EC001288	ETIM 9.0	EC001288
ECLASS 9.0	27-40-06-29	ECLASS 9.1	27-40-06-29
ECLASS 10.0	27-40-06-29	ECLASS 11.0	27-28-11-04
ECLASS 12.0	27-28-11-04	ECLASS 13.0	27-28-11-04

Approvals

ROHS	Conform
------	---------

Downloads


Catalogues	Catalogues in PDF-format
------------	--

THM ET 200SP 12.8/31 GE

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings



THM ET 200SP 12.8/31 GE**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Ink ribbons**

These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

Type	RIBBON MM 110/360 SW	Version
Order No.	2005070000	Ink ribbon
GTIN (EAN)	4050118390049	
Qty.	1 pc(s).	