

**VFSKHI/0,1-0,5/288****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Insulated tab-connector sleeves made from PVC  
with copper sleeve**

- Commercially available designs
- Not soldered
- With conical entry funnel

**General ordering data**

|            |                                                                                                                     |
|------------|---------------------------------------------------------------------------------------------------------------------|
| Version    | cable lug, terminal end, Insulated cable connector, 0.5 mm <sup>2</sup> , 0.1 mm <sup>2</sup> - 0.5 mm <sup>2</sup> |
| Order No.  | <a href="#">1491630000</a>                                                                                          |
| Type       | VFSKHI/0,1-0,5/288                                                                                                  |
| GTIN (EAN) | 4050118301489                                                                                                       |
| Qty.       | 100 pc(s).                                                                                                          |

**VFSKHI/0,1-0,5/288****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

|            |        |
|------------|--------|
| Net weight | 0.37 g |
|------------|--------|

**Connectors**

|                               |                     |                               |                     |
|-------------------------------|---------------------|-------------------------------|---------------------|
| Conductor cross-section       | 0.5 mm <sup>2</sup> | Conductor cross-section, max. | 0.5 mm <sup>2</sup> |
| Conductor cross-section, min. | 0.1 mm <sup>2</sup> | Identification colour         | yellow              |
| Insulation                    | Available           | Length 1 (l1)                 | 16 mm               |
| Length 2 (l2)                 | 6.4 mm              | Material/plastic              | PVC                 |
| Plug-in density (d3)          | 0.8 mm              | Plug-in width (d2)            | 2.8 mm              |

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC000516    | ETIM 7.0    | EC000516    |
| ETIM 8.0    | EC000516    | ETIM 9.0    | EC000516    |
| ECLASS 9.0  | 27-44-03-92 | ECLASS 9.1  | 27-40-02-90 |
| ECLASS 10.0 | 27-44-03-92 | ECLASS 11.0 | 27-44-03-92 |
| ECLASS 12.0 | 27-44-03-92 | ECLASS 13.0 | 27-44-03-92 |

**Environmental Product Compliance**

|            |                                       |
|------------|---------------------------------------|
| REACH SVHC | Lead 7439-92-1                        |
| SCIP       | 7b42d2b9-0a0f-4f66-a989-e9bfbfbefb1b3 |

**Approvals**

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

**Downloads**

|            |                                          |
|------------|------------------------------------------|
| Catalogues | <a href="#">Catalogues in PDF-format</a> |
|------------|------------------------------------------|

**VFSKHI/0,1-0,5/288**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings



**VFSKHI/0,1-0,5/288****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****Crimping tools****Crimping tools for insulated connectors**

cable lugs, terminal pins, parallel and serial connectors, plug-in connectors

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation
- With stop for exact positioning of the contacts.
- Tested to DIN EN 60352 part 2

**General ordering data**

|            |                            |                                                                                               |
|------------|----------------------------|-----------------------------------------------------------------------------------------------|
| Type       | CTI 6 G                    | Version                                                                                       |
| Order No.  | <a href="#">9202850000</a> | Pressing tool, Tool for insulated cable connectors, 0.5mm <sup>2</sup> , 6mm <sup>2</sup> ,   |
| GTIN (EAN) | 4032248517855              | Oval crimping, Parallel crimp                                                                 |
| Qty.       | 1 pc(s).                   |                                                                                               |
| Type       | HTI 15                     | Version                                                                                       |
| Order No.  | <a href="#">9014400000</a> | Pressing tool, Tool for insulated cable connectors, 0.5mm <sup>2</sup> , 2.5mm <sup>2</sup> , |
| GTIN (EAN) | 4008190159412              | Double crimp                                                                                  |
| Qty.       | 1 pc(s).                   |                                                                                               |
| Type       | CTI 6                      | Version                                                                                       |
| Order No.  | <a href="#">9006120000</a> | Pressing tool, Crimping tool for contacts, 0.5mm <sup>2</sup> , 6mm <sup>2</sup> , Oval       |
| GTIN (EAN) | 4008190044527              | crimping, Double crimp                                                                        |
| Qty.       | 1 pc(s).                   |                                                                                               |