

FSKI/0,5-1,0/288**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Insulated tab connector made from PVC with copper sleeve**

- Commercially available designs
- Not soldered
- With conical entry funnel

General ordering data

| | |
|------------|---|
| Version | cable lug, terminal end, Insulated cable connector, 0.5 mm ² , 0.5 mm ² - 1 mm ² |
| Order No. | 1491790000 |
| Type | FSKI/0,5-1,0/288 |
| GTIN (EAN) | 4050118301540 |
| Qty. | 100 pc(s). |

FSKI/0,5-1,0/288**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

| | |
|------------|---------|
| Net weight | 0.765 g |
|------------|---------|

Connectors

| | | | |
|-------------------------------|---------------------|-------------------------------|-------------------|
| Conductor cross-section | 0.5 mm ² | Conductor cross-section, max. | 1 mm ² |
| Conductor cross-section, min. | 0.5 mm ² | Identification colour | red |
| Insulation | Available | Length 1 (l1) | 19.2 mm |
| Material/plastic | PVC | Plug-in density (d3) | 0.8 mm |
| Plug-in width (d2) | 2.8 mm | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC000516 | ETIM 7.0 | EC000516 |
| ETIM 8.0 | EC000516 | ETIM 9.0 | EC000516 |
| ECLASS 9.0 | 27-44-03-92 | ECLASS 9.1 | 27-40-02-90 |
| ECLASS 10.0 | 27-44-03-92 | ECLASS 11.0 | 27-44-03-92 |
| ECLASS 12.0 | 27-44-03-92 | ECLASS 13.0 | 27-44-03-92 |

Environmental Product Compliance

| | |
|------------|---------------------------------------|
| REACH SVHC | Lead 7439-92-1 |
| SCIP | 7b42d2b9-0a0f-4f66-a989-e9bfbfbefb1b3 |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|------------|--|
| Catalogues | Catalogues in PDF-format |
| Brochures | |

FSKI/0,5-1,0/288

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Drawings

