

KP-M10/-240**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



The use of insulated connectors guarantees users consistent electrical connection quality in the long term.

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

General ordering data

| | |
|------------|--|
| Version | cable lug, terminal end, 240 mm ² |
| Order No. | 1498390000 |
| Type | KP-M10/-240 |
| GTIN (EAN) | 4050118307818 |
| Qty. | 20 pc(s). |

KP-M10/-240**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

| | |
|------------|----------|
| Net weight | 271.04 g |
|------------|----------|

Technical data

| | |
|---------|----------------------------|
| Version | DIN series 46235, standard |
|---------|----------------------------|

Connectors

| | | | |
|--------------------------------|---------------------|--------------------------------|---------------|
| Conductor cross-section | 240 mm ² | Connection length (l) | 92 mm |
| Flange width (b) | 42 mm | Hole | M10 |
| Identification number Cu | 28 K | Inside diameter of flange (d2) | 10.5 mm |
| Inside diameter of shaft (d1) | 21.5 mm | Insulation | not available |
| Outside diameter of shaft (d3) | 29 mm | Shaft length (a) | 40 mm |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC001050 | ETIM 7.0 | EC001050 |
| ETIM 8.0 | EC001050 | ETIM 9.0 | EC001050 |
| ECLASS 9.0 | 27-40-02-03 | ECLASS 9.1 | 27-40-02-03 |
| ECLASS 10.0 | 27-40-02-03 | ECLASS 11.0 | 27-40-02-03 |
| ECLASS 12.0 | 27-40-02-03 | ECLASS 13.0 | 27-40-02-03 |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|------------|--|
| Catalogues | Catalogues in PDF-format |
| Brochures | |

KP-M10/-240

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

