

CRIMPSET PZ 10 SQR**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Crimp sets

General ordering data

Version	Assortment crimping tool, Crimping tool: PZ 10 SQR, Stripping tool: STRIPAX, Crimping range, min.: 0.14, Colour code: Weidmüller
Order No.	1542280000
Type	CRIMPSET PZ 10 SQR
GTIN (EAN)	4050118347050
Qty.	1 pc(s).
Packaging	Plastic box

Creation date April 29, 2024 8:37:47 PM CEST

Catalogue status 20.04.2024 / We reserve the right to make technical changes.

CRIMPSET PZ 10 SQR**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Depth	261 mm	Depth (inches)	10.276 inch
Height	57 mm	Height (inches)	2.244 inch
Width	338 mm	Width (inches)	13.307 inch
Net weight	1,803 g		

Technical data

Description of article	Set includes crimping tool up to 10 mm ² square, stripping tool and wire-end ferrules in Weidmüller colour code
------------------------	----------------------------------------------------------------------------------------------------------------------------

Assortments

Colour code	Weidmüller	Crimping range, max.	10 mm ²
Crimping range, min.	0.14 mm ²	Crimping tool	PZ 10 SQR
Number of AEH	2,900 pcs.	Packaging	Plastic box
Stripping tool	STRIPAX		

Classifications

ETIM 6.0	EC000524	ETIM 7.0	EC000524
ETIM 8.0	EC000524	ETIM 9.0	EC000524
ECLASS 9.0	27-40-02-18	ECLASS 9.1	27-40-02-18
ECLASS 10.0	27-40-02-18	ECLASS 11.0	27-40-02-18
ECLASS 12.0	27-40-02-18	ECLASS 13.0	27-40-02-18

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	1eacbb3e-7931-4ebb-9179-f29fd9b50028

Downloads

Catalogues	Catalogues in PDF-format
------------	------------------------------------------

CRIMPSET PZ 10 SQR

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

packed loose in polythene bag



- supplied loose in polybag
- Weidmüller colour code
- DIN colour code

General ordering data

Type	H0,5/14 OR	Version	Packaging
Order No.	0690700000	Wire-end ferrule, Standard, 10 mm, 8 mm, orange	loose
GTIN (EAN)	4008190015770		
Qty.	500 pc(s).		

Tools



- Stripping tools with automatic self-adjustment
- For flexible and solid conductors
- Ideally suitable for mechanical and plant engineering, railway and rail traffic, wind energy, robot technology, explosion protection as well as marine, offshore and ship building sectors
- Stripping length adjustable via end stop
- Automatic opening of clamping jaws after stripping
- No fanning-out of individual conductors
- Adjustable to diverse insulation thicknesses
- Double-insulated cables in two process steps without special adjustment
- No play in self-adjusting cutting unit
- Long service life
- Optimised ergonomic design

General ordering data

Type	STRIPAX	Version
Order No.	9005000000	Tools, Stripping and cutting tool
GTIN (EAN)	4008190072506	
Qty.	1 pc(s).	

CRIMPSET PZ 10 SQR**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****packed loose in polythene bag**

- supplied loose in poly-bag
- Weidmüller colour code
- DIN colour code

General ordering data

Type	H1,5/14 R	Version		Packaging	
Order No.	0463100000	Wire-end ferrule, Standard, 10 mm, 8 mm, red		loose	
GTIN (EAN)	4008190065089				
Qty.	500 pc(s).				

packed loose in polythene bag

- supplied loose in polybag
- DIN colour code
- other colour code

General ordering data

Type	H4,0/20D GR	Version		Packaging	
Order No.	9019200000	Wire-end ferrule, Standard, 14 mm, 12 mm, grey		loose	
GTIN (EAN)	4008190126575				
Qty.	500 pc(s).				

CRIMPSET PZ 10 SQR

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Crimping tools

**Crimping tools for wire end ferrules, with and without plastic collars**

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation

General ordering data

Type	PZ 10 SQR	Version
Order No.	1445080000	Crimping tool for wire-end ferrules, 0.14mm ² , 10mm ² , Square crimp
GTIN (EAN)	4050118250152	
Qty.	1 pc(s).	

packed loose in polythene bag



- supplied loose in polybag
- Weidmüller colour code
- DIN colour code
- other colour code

General ordering data

Type	H0,75/14 W	Version	Packaging
Order No.	0462900000	Wire-end ferrule, Standard, 10 mm, 8 mm, white	loose
GTIN (EAN)	4008190033248		
Qty.	500 pc(s).		

CRIMPSET PZ 10 SQR**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Conductor nom. cross-section 10mm²**

- supplied loose in polybag
- Weidmüller colour code
- DIN colour code
- other colour code

General ordering data

Type	H10,0/22 EB	Version		Packaging	
Order No.	0534200000	Wire-end ferrule, Standard, 15 mm, 12 mm, Ivory		loose	
GTIN (EAN)	4008190033460				
Qty.	100 pc(s).				

packed loose in polythene bag

- supplied loose in polybag
- Weidmüller colour code
- DIN colour code

General ordering data

Type	H1,0/14 GE	Version		Packaging	
Order No.	0463000000	Wire-end ferrule, Standard, 10 mm, 8 mm, yellow		loose	
GTIN (EAN)	4008190024697				
Qty.	500 pc(s).				

CRIMPSET PZ 10 SQR**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****packed loose in polythene bag**

- supplied loose in polybag
- DIN colour code
- other colour code

General ordering data

Type	H2,5/15D BL	Version		Packaging	
Order No.	9019160000	Wire-end ferrule, Standard, 10 mm, 8 mm, blue		loose	
GTIN (EAN)	4008190028732				
Qty.	500 pc(s).				

Case

- Body of case made from unbreakable polypropylene
- Portable and uncluttered storage in minimum space
- With two sturdy sliding catches
- Assortment cases and boxes can be placed upright and can be stacked safely without any sliding
- can be subdivided with inserts

General ordering data

Type	KOFFER PSC4-01	Version	
Order No.	9028860000	Tools, Assortment box	
GTIN (EAN)	4032248304608		
Qty.	1 pc(s).		

CRIMPSET PZ 10 SQR

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Conductor nom. cross-section 6.0mm²

- supplied loose in poly-bag
- Weidmüller colour code
- DIN colour code
- other colour code

General ordering data

Type	H6,0/20 SW	Version		Packaging	
Order No.	0533500000	Wire-end ferrule, Standard, 14 mm, 12 mm, black		loose	
GTIN (EAN)	4008190183905				
Qty.	100 pc(s).				