

**MARKO-C. 50X50X50 B/DR.****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**General ordering data**

Version	Device markers, Device markers, 50 x 50 mm, yellow
Order No.	<a href="#">1700540001</a>
Type	MARKO-C. 50X50X50 B/DR.
GTIN (EAN)	4008190894306
Qty.	10 pc(s).

**MARKO-C. 50X50X50 B/DR.****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Depth	0.05 mm	Depth (inches)	0.002 inch
Height	50 mm	Height (inches)	1.969 inch
Width	50 mm	Width (inches)	1.969 inch
Net weight	0.603 g		

**Temperatures**

Operating temperature range	-29...80 °C
-----------------------------	-------------

**General data**

Adhesive	Permanent acrylic copolymer		
Colour	yellow		
Colour of printing	black		
Material	Acrylic-coated fibre webbing		
Material colour according to resistance code	4		
Number of markers per combination	1 Label sheet = 7 Device markers		
Number of markers per packaging unit	Number of combinations per packaging unit	10	
	Number of markers per combination	7	
	Form of supply	Label sheet	
Number of markers per packaging unit	70		
Operating temperature range	-29...80 °C		
Operating temperature range, max.	80 °C		
Operating temperature range, min.	-29 °C		
Printed characters	Symbols		
Printing	Lightning flash in triangle		
Version	Self-adhesive		
Width	50 mm		

**Classifications**

ETIM 6.0	EC001288	ETIM 7.0	EC001288
ETIM 8.0	EC001288	ETIM 9.0	EC001288
ECLASS 9.0	27-40-06-29	ECLASS 9.1	27-40-06-29
ECLASS 10.0	27-40-06-29	ECLASS 11.0	27-28-11-04
ECLASS 12.0	27-28-11-04	ECLASS 13.0	27-28-11-04

**Approvals**

ROHS	Conform
------	---------

**Downloads**

Catalogues	<a href="#">Catalogues in PDF-format</a>
------------	--

### MARKO-C. 50X50X50 B/DR.

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

