

**DFFC .5-1.0 ZRV1.5****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image**

Similar to illustration

We offer a broad portfolio of mounting support for easy handling and supplementation of our products. From various tools to insulating sleeves and various screws, our components are matched to each other down to the last detail and thus facilitate assembly in compliance with the respective standards and protective regulations.

**General ordering data**

Version	Crimp contact (terminal), 1.5 mm <sup>2</sup>
Order No.	<a href="#">1705320000</a>
Type	DFFC .5-1.0 ZRV1.5
GTIN (EAN)	4008190948566
Qty.	500 pc(s).

**DFFC .5-1.0 ZRV1.5****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

Net weight	0.22 g
------------	--------

**Temperatures**

Operating temperature	130 °C
-----------------------	--------

**Material data**

Material	Plastic	Colour	silver
----------	---------	--------	--------

**System specifications**

Version	for holding 0.5 ... 1.0 mm <sup>2</sup>
---------	---

**Additional technical data**

Installation advice	Direct mounting
---------------------	-----------------

**Conductors for clamping (rated connection)**

Type of connection	Crimp contact
--------------------	---------------

**General**

Installation advice	Direct mounting
---------------------	-----------------

**Rating data**

Rated cross-section	1.5 mm <sup>2</sup>	Volume resistance according to IEC 60947-7-x	1.83 mΩ
Power loss in accordance with IEC 60947-7-x	0.56 W		

**Classifications**

ETIM 6.0	EC000796	ETIM 7.0	EC000796
ETIM 8.0	EC000796	ETIM 9.0	EC000796
ECLASS 9.0	27-44-02-04	ECLASS 9.1	27-44-02-04
ECLASS 10.0	27-44-02-04	ECLASS 11.0	27-44-02-04
ECLASS 12.0	27-44-02-04	ECLASS 13.0	27-44-02-04

**Environmental Product Compliance**

REACH SVHC	/
RoHS Compliance Status	Compliant without exemption

**Approvals**

ROHS	Conform
------	---------

### DFFC .5-1.0 ZRV1.5

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Downloads

Engineering Data	<a href="#">CAD data – STEP</a>
User Documentation	<a href="#">StorageConditionsTerminalBlocks</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	<a href="#">CAT 1 TERM 16/17 EN</a>