

VP M16-EXE SW**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Similar to illustration**

For sealing surplus threaded holes to maintain the IP class of protection

General ordering data

Version	VPK EX (Ex blanking plug in plastic), Blanking plug, in closed state, M 16, 15 mm, IP66, IP68, Polyamide
Order No.	1737070000
Type	VP M16-EXE SW
GTIN (EAN)	4008190956547
Qty.	100 pc(s).

VP M16-EXE SW**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Height	19 mm	Height (inches)	0.748 inch
Length	19 mm	Length (inches)	0.748 inch
Diameter	16 mm	Wall thickness, min.	0.5 mm
Wall thickness, max.	14 mm	Net weight	2.67 g

Temperatures

Operating temperature	-20 °C...80 °C
-----------------------	----------------

Technical properties

Protection degree	IP54, IP66
-------------------	------------

Technical data

Protection degree	IP54, IP66	Colour	Deep black
Protection degree	IP54, IP66		

Classifications

ETIM 6.0	EC000451	ETIM 7.0	EC000451
ETIM 8.0	EC000451	ETIM 9.0	EC000451
ECLASS 9.0	27-14-44-25	ECLASS 9.1	27-14-44-35
ECLASS 10.0	27-14-44-25	ECLASS 11.0	27-14-44-25
ECLASS 12.0	27-14-08-05	ECLASS 13.0	27-14-08-05

Approvals

Approvals



ROHS	Conform
------	---------

Downloads


Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format
Brochures	

VP M16-EXE SW

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings



VP M16-EXE SW**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Brass lock nuts, nickel-plated**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	SKMU M16 MS	Version
Order No.	1736990000	SKMU MS (brass locknut), Locknut, M 16, 2.8 mm, Brass, nickel-
GTIN (EAN)	4008190956462	plated
Qty.	100 pc(s).	

Neoprene flat gasket - GWDR NP

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	GWDR M16-NP	Version
Order No.	1736230000	GWDR NP (flat gasket - neoprene), Sealing ring, M 16, Neoprene
GTIN (EAN)	4008190956028	
Qty.	50 pc(s).	