

**SCHS3 K****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**General ordering data**

|            |   |
|------------|---|
| Version    | Device markers, Accessories x 10 mm, PVC,<br>Colour: black, Self-adhesive |
| Order No.  | <a href="#">1753480000</a>  |
| Type       | SCHS3 K   |
| GTIN (EAN) | 4032248014347   |
| Qty.       | 1 pc(s).  |

**SCHS3 K****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

|            |          |                 |            |
|------------|----------|-----------------|------------|
| Depth      | 6 mm     | Depth (inches)  | 0.236 inch |
| Height     | 1,000 mm | Height (inches) | 39.37 inch |
| Width      | 10 mm    | Width (inches)  | 0.394 inch |
| Net weight | 22 g     |                 |            |

**Temperatures**

|                             |             |
|-----------------------------|-------------|
| Operating temperature range | -20...80 °C |
|-----------------------------|-------------|

**General data**

|  |                            |           |
|--|----------------------------|-----------|
| Adhesive                                     | Double-sided adhesive tape |           |
| Application/manufacturer                     | Self-adhesive              |           |
| Colour                                       | black                      |           |
| Halogen                                      | No                         |           |
| Material                                     | PVC                        |           |
| Material colour according to resistance code | 0                          |           |
| Number of markers per combination            | 1 MultiCard = Accessories  |           |
| Number of markers per packaging unit         | Form of supply             | MultiCard |
| Operating temperature range                  | -20...80 °C                |           |
| Operating temperature range, max.            | 80 °C                      |           |
| Operating temperature range, min.            | -20 °C                     |           |
| UL 94 flammability rating                    | V-0                        |           |
| Version                                      | Self-adhesive              |           |
| Width  | 10 mm                      |           |

**Device markers**

|         |    |
|---------|----|
| Halogen | No |
|---------|----|

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC001288    | ETIM 7.0    | EC001288    |
| ETIM 8.0    | EC001288    | ETIM 9.0    | EC001288    |
| ECLASS 9.0  | 27-40-06-29 | ECLASS 9.1  | 27-40-06-29 |
| ECLASS 10.0 | 27-40-06-29 | ECLASS 11.0 | 27-28-11-04 |
| ECLASS 12.0 | 27-28-11-04 | ECLASS 13.0 | 27-28-11-04 |

**Approvals**

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

**Downloads**

|            |  |
|------------|--|
| Catalogues | <a href="#">Catalogues in PDF-format</a> |
|------------|--|

### SCHS3 K

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings



**SCHS3 K****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****Blank**

ESG is the tried-and-tested marker in MultiCard format for use on many well-known electrical devices. The result is high-quality device marking with a high-contrast appearance.

Various types are available for devices from manufacturers like Siemens, ABB, Beckhoff etc.

Advantages at a glance:

- Tags for universal usage, self-adhesive or clip-on tags, depending on type
- For aligned equipment, e.g. circuit breakers, we supply ESG markers for clipping onto tag rails
- Individual laser-quality printing according to specifications

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

**General ordering data**

|            |                            |  |
|------------|----------------------------|--|
| Type       | ESG 7/20 SIRIUS MC NE GE   | Version  |
| Order No.  | <a href="#">1736181687</a> | ESG, Device markers x 20 mm, PA 66, Colour: yellow, pluggable    |
| GTIN (EAN) | 4032248208265              |  |
| Qty.       | 200 pc(s).                 |  |
| Type       | ESG 7/20 SIRIUS MC NE WS   | Version  |
| Order No.  | <a href="#">1736181044</a> | ESG, Device markers x 20 mm, PA 66, Colour: white, pluggable     |
| GTIN (EAN) | 4008190985950              |  |
| Qty.       | 200 pc(s).                 |  |
| Type       | ESG 7/20 SIRIUS MC NE TU   | Version  |
| Order No.  | <a href="#">1736181696</a> | ESG, Device markers x 20 mm, PA 66, Colour: Turquoise, pluggable |
| GTIN (EAN) | 4008190985967              |  |
| Qty.       | 200 pc(s).                 |  |

**SCHS3 K****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****Custom printing**

ESG is the tried-and-tested marker in MultiCard format for use on many well-known electrical devices. The result is high-quality device marking with a high-contrast appearance.

Various types are available for devices from manufacturers like Siemens, ABB, Beckhoff etc.

Advantages at a glance:

- Tags for universal usage, self-adhesive or clip-on tags, depending on type
- For aligned equipment, e.g. circuit breakers, we supply ESG markers for clipping onto tag rails
- Individual laser-quality printing according to specifications

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

**General ordering data**

|            |                            |   |
|------------|----------------------------|---|
| Type       | ESG 7/20 SIRIUS MC SDR     | Version   |
| Order No.  | <a href="#">1766650000</a> | ESG, Device markers x 20 mm, PA 66, Colour: To customer |
| GTIN (EAN) | 4032248065547              | specification, pluggable                                |
| Qty.       | 40 pc(s).                  |   |