

LM WO 15/70 WS**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration



Self-adhesive polyester labels which are suitable for A4 office laser printer.

General ordering data

Version	LaserMark, Conductor and cable markers, 8.2 - 14.3 mm, 15 x 70 mm, white
Order No.	1759871044
Type	LM WO 15/70 WS
GTIN (EAN)	403224802695 1
Qty.	10 pc(s).

LM WO 15/70 WS

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	0.025 mm	Depth (inches)	0.001 inch
Height	15 mm	Height (inches)	0.591 inch
Width	70 mm	Width (inches)	2.756 inch
Net weight	10.4 g		

Temperatures

Operating temperature range	-40...150 °C
-----------------------------	--------------

General data

Adhesive	Acrylate	
Colour	white	
Halogen	No	
Material	Polyester film	
Material colour according to resistance code	9	
Number of markers per combination	1 Label sheet = 52 Conductor and cable markers	
Number of markers per packaging unit	520	
Number of markers per packaging unit	Number of combinations per packaging unit	10
	Form of supply	Label sheet
	Number of markers per combination	52
Number per sheet	52	
Operating temperature range	-40... 150 °C	
Operating temperature range, max.	150 °C	
Operating temperature range, min.	-40 °C	
Size of labelling field	15 x 30 mm	
Type of printing	neutral	
UL 94 flammability rating	V-0	
Version	Self-adhesive	
Width	70 mm	

Conductor and cable markers

Conductor O.D.	8.2 - 14.3 mm	Conductor O.D., max.	14.3 mm
Conductor O.D., min.	8.2 mm	Conductor cross-section, max.	50 mm ²
Conductor cross-section, min.	16 mm ²	Cross-section for connected wire	16 - 50 mm ²
Halogen	No	Text field height	30 mm
Text field width	14.98 mm		

Classifications

ETIM 6.0	EC001530	ETIM 7.0	EC001530
ETIM 8.0	EC001530	ETIM 9.0	EC001530
ECLASS 9.0	27-40-04-01	ECLASS 9.1	27-40-04-01
ECLASS 10.0	27-40-04-01	ECLASS 11.0	27-28-11-02
ECLASS 12.0	27-28-11-02	ECLASS 13.0	27-28-11-02

Approvals

ROHS	Conform
------	---------

LM WO 15/70 WS

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Downloads

Engineering Data	CAD data – STEP
Engineering Data	Zuken E3.S
Catalogues	Catalogues in PDF-format

LM WO 15/70 WS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

