

**MK 3/3 B 412****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Multi-pole terminal strips are suitable for wiring in junction boxes and small distribution boxes. The different numbers of poles offer the possibilities of direct mounting inside the housings.

**General ordering data**

Version	Single- and multi-pole terminal strip, Screw connection, 2.5 mm <sup>2</sup> , 400 V, Number of poles: 3, 72.75 mm, medium yellow
Order No.	<a href="#">1784480000</a>
Type	MK 3/3 B 412
GTIN (EAN)	4032248191147
Qty.	50 pc(s).

## MK 3/3 B 412

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	16.1 mm	Depth (inches)	0.634 inch
Height	16.1 mm	Height (inches)	0.634 inch
Width	72.75 mm	Width (inches)	2.864 inch
Net weight	11.04 g		

## Temperatures

Storage temperature	-25 °C...55 °C
---------------------	----------------

## Material data

Colour	medium yellow
--------	---------------

## Additional technical data

Explosion-tested version	No
--------------------------	----

## Conductors for clamping (additional connection)

Connection type, additional connection	Screw connection
--	------------------

## Conductors for clamping (rated connection)

Type of connection	Screw connection
--------------------	------------------

## General

Number of poles	3
-----------------	---

## Rating data

Rated cross-section	2.5 mm <sup>2</sup>	Rated voltage	400 V
Rated DC voltage	400 V	Volume resistance according to IEC 60947-7-x	1.33 mΩ
Power loss in accordance with IEC 60947-7-x	0.77 W		

## Classifications

ETIM 6.0	EC001284	ETIM 7.0	EC001284
ETIM 8.0	EC001284	ETIM 9.0	EC001284
ECLASS 9.0	27-14-11-06	ECLASS 9.1	27-14-11-06
ECLASS 10.0	27-14-11-06	ECLASS 11.0	27-14-11-06
ECLASS 12.0	27-14-11-06	ECLASS 13.0	27-14-11-06

## Approvals

Approvals



ROHS	Conform
------	---------

### MK 3/3 B 412

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Downloads

Approval/Certificate/Document of Con-  
formity

[UKCA declaration of conformity](#)

Engineering Data

[CAD data – STEP](#)

Catalogues

[Catalogues in PDF-format](#)