

ET S7-300-TU-A4-2**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration

The ET S7 DIN-A4 non-adhesive labels are used to label the S300, S400 and S7 modules from Siemens. Customised laser printing is possible using Weidmüller's M-Print® Pro software.

- Background colours yellow or turquoise with black printing (boxes)
- Labels can be easily separated (not adhesive)

General ordering data

Version	LaserMark, Device markers, 208 x 17.3 mm, Siemens, Turquoise
Order No.	1865460000
Type	ET S7-300-TU-A4-2
GTIN (EAN)	4032248434138
Qty.	10 pc(s).

ET S7-300-TU-A4-2**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Depth	0.1 mm	Depth (inches)	0.004 inch
Height	208 mm	Height (inches)	8.189 inch
Width	17.3 mm	Width (inches)	0.681 inch
Net weight	31.1 g		

Temperatures

Operating temperature range	-40...80 °C
-----------------------------	-------------

General data

Application/manufacture	Siemens		
Approval acc. to UL 969	No		
Colour	Turquoise		
Halogen	Yes		
Material	Vinyl film		
Number of markers per combination	1 Label sheet = 22 Device markers		
Number of markers per packaging unit	Number of markers per combination	22	
	Form of supply	Label sheet	
	Number of combinations per packaging unit	10	
Number of markers per packaging unit	220		
Number per sheet	22		
Operating temperature range	-40...80 °C		
Operating temperature range, max.	80 °C		
Operating temperature range, min.	-40 °C		
Printing method	Laser print		
UL 94 flammability rating	HB		
Width	17.3 mm		

Device markers

Halogen	Yes
---------	-----

Classifications

ETIM 6.0	EC001288	ETIM 7.0	EC001288
ETIM 8.0	EC001288	ETIM 9.0	EC001288
ECLASS 9.0	27-40-06-29	ECLASS 9.1	27-40-06-29
ECLASS 10.0	27-40-06-29	ECLASS 11.0	27-28-11-04
ECLASS 12.0	27-28-11-04	ECLASS 13.0	27-28-11-04

Approvals

ROHS	Conform
------	---------

Downloads

Catalogues	Catalogues in PDF-format
------------	--

ET S7-300-TU-A4-2

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

