

**SAIB-VSC-4P/250/7-OB****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Individual cable lengths are often required nowadays. In order to meet these demands, Weidmüller offers a wide range of plug-in connectors for custom assembly. Customisable valve plugs are used frequently in special-purpose machine engineering. Such plugs are used to connect solenoid valves. The valve plugs are available in all standard design types. The range includes the design types A, B Industrial, B acc. to DIN, C Industrial and C acc. to DIN. The valve plugs are available in 3 and 4-pole versions without cables. A flat gasket seal is included which, when screwed on, guarantees IP 65 protection.

**General ordering data**

Version	Field attachable connector, Valve plug, Socket, angled
Order No.	<a href="#">1873210000</a>
Type	SAIB-VSC-4P/250/7-OB
GTIN (EAN)	4032248495436
Qty.	1 pc(s).

## SAIB-VSC-4P/250/7-OB

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Net weight	13 g
------------	------

## Technical data customisable plug-in connectors

All valve plugs are fitted with protective circuits		Cable diameter	
	Without circuitry		4...6 mm
Cable diameter, max.	6 mm	Cable diameter, min.	4 mm
Cable glands	PG 7	Coding	Industrial design C (9.4 mm)
Conductor cross-section, max.	1.5 mm <sup>2</sup>	Conductor cross-section, min.	0.34 mm <sup>2</sup>
Connection cross-section, max.	1.5 mm <sup>2</sup>	Connection cross-section, min.	0.34 mm <sup>2</sup>
Contact surface	Ni	Housing main material	PA 6 GF
Insulation strength	10 <sup>8</sup> Ω	LED	No
Number of poles	4	Plugging cycles	≤ 50
Pollution severity	3	Protection degree	IP65
Rated current	10 A	Temperature range of housing	-25...+85 °C
Type of connection	Screw connection		

## Classifications

ETIM 6.0	EC002062	ETIM 7.0	EC003623
ETIM 8.0	EC003623	ETIM 9.0	EC003623
ECLASS 9.0	27-44-01-05	ECLASS 9.1	27-44-01-05
ECLASS 10.0	27-44-01-05	ECLASS 11.0	27-44-01-05
ECLASS 12.0	27-44-01-05	ECLASS 13.0	27-44-01-05

## Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

## Approvals

Approvals



ROHS	Conform
------	---------

## Downloads

Engineering Data	<a href="#">CAD data – STEP</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	<a href="#">FL FIELDWIRING EN</a> <a href="#">FL FIELDWIRING EN</a>