

ETO SM 22/22 TRANSPAR.**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration

SM is a MultiCard marker for labelling control and signalling devices. The tags are clipped into the carriers or attached by means of the adhesive film already fitted to them. Customised tags can be created with the PrintJet CONNECT or Plotter marking systems.

- Users can quickly produce tags to suit their needs
- No need to stock expensive standard tags
- Highly resistant printing quality when using the PrintJet as a substitute for engraving
- For extreme demands, we recommend the ETO SM protective film
- Holders can be used for the 22-mm or 30-mm-diameter push-buttons from Siemens, ABB, Moeller and Télémécanique

For custom printing: Please send us a file of our labelling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Version	SwitchMark, Protective cap, 22 x 22 mm, Transparent
Order No.	1880720000
Type	ETO SM 22/22 TRANSPAR.
GTIN (EAN)	4032248480883
Qty.	10 pc(s).

ETO SM 22/22 TRANSPAR.**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Depth	0.2 mm	Depth (inches)	0.008 inch
Height	22 mm	Height (inches)	0.866 inch
Width	22 mm	Width (inches)	0.866 inch
Net weight	12.6 g		

Temperatures

Operating temperature range	-20...80 °C
-----------------------------	-------------

General data

Adhesive	Permanent acrylic copolymer	
Colour	Transparent	
Halogen	No	
Material	Polyester film	
Number of markers per combination	1 MultiCard = Protective cap	
Number of markers per packaging unit	Form of supply	MultiCard
Number per sheet	112	
Operating temperature range	-20...80 °C	
Operating temperature range, max.	80 °C	
Operating temperature range, min.	-20 °C	
UL 94 flammability rating	HB	
Width	22 mm	

Device markers

Halogen	No
---------	----

Classifications

ETIM 6.0	EC001288	ETIM 7.0	EC001288
ETIM 8.0	EC001288	ETIM 9.0	EC001288
ECLASS 9.0	27-40-06-29	ECLASS 9.1	27-40-06-29
ECLASS 10.0	27-40-06-29	ECLASS 11.0	27-28-11-04
ECLASS 12.0	27-28-11-04	ECLASS 13.0	27-28-11-04

Approvals

ROHS	Conform
------	---------

Downloads

Catalogues	Catalogues in PDF-format
------------	--

ETO SM 22/22 TRANSPAR.

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Drawings

