


ZQV 4/20 GE**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image**

The plug-in cross-connections feature easy handling and quick installation. This saves a great deal of time during installation in comparison with screwed solutions.

General ordering data

Version	Z-series, Cross-connector, For the terminals, Number of poles: 20
Order No.	1909010000
Type	ZQV 4/20 GE
GTIN (EAN)	4032248535637
Qty.	20 pc(s).

ZQV 4/20 GE

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	31.6 mm	Depth (inches)	1.244 inch
Height	120.3 mm	Height (inches)	4.736 inch
Width	2.8 mm	Width (inches)	0.11 inch
Net weight	18.195 g		

Temperatures

Storage temperature	-25 °C...55 °C	Continuous operating temp., min.	-60
Continuous operating temp., max.	130		

Material data

Material	Wemid	Colour	yellow
UL 94 flammability rating	V-0		

System specifications

Version	For the terminals
---------	-------------------

Additional technical data

Installation advice	Direct mounting	Type of fixing	Plugged
---------------------	-----------------	----------------	---------

Cross-connector

Rated current, multi-pole	32 A	Type	Cross-connector
---------------------------	------	------	-----------------

Dimensions

Pitch in mm (P)	6.1 mm
-----------------	--------

General

Installation advice	Direct mounting	Number of poles	20
---------------------	-----------------	-----------------	----

Rating data

Rated current	32 A
---------------	------

Classifications

ETIM 6.0	EC000489	ETIM 7.0	EC000489
ETIM 8.0	EC000489	ETIM 9.0	EC000489
ECLASS 9.0	27-14-11-40	ECLASS 9.1	27-14-11-40
ECLASS 10.0	27-14-11-40	ECLASS 11.0	27-14-11-40
ECLASS 12.0	27-14-11-40	ECLASS 13.0	27-25-03-03

Important note

Product information	Due to stability and temperature reasons It is only possible to break out 60% of contact elements The usage of cross connectors reduces the rated voltage to 400VThe voltage reduced to 25V if cut cross connection with blank cut edges are used
---------------------	---

ZQV 4/20 GE**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Approvals**

ROHS	Conform
------	---------

Downloads

Approval/Certificate/Document of Conformity	Confirmation of Standards EN 45545-2_2020-10
---	--

Engineering Data	CAD data – STEP
------------------	---------------------------------

Engineering Data	Zuken E3.S
------------------	----------------------------

User Documentation	Operating instructions_ZDU1.5-ZDU35_ZQV.pdf StorageConditionsTerminalBlocks User Manual ZQV 2.5
--------------------	---

Catalogues	Catalogues in PDF-format
------------	--

Brochures	
-----------	--