

**SAIE-M8R-4-0.5U-FP-M8****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Various build-in connectors are required for the connections on the device side of the sensor/actuator cabling. These are available in the versions M12, M8 and M5.

**General ordering data**

Version	Built-in plugs, M8 snap, pin, straight, Mounting thread: M8, Number of poles: 4, Strand / cable length: 0.5 m
Order No.	<a href="#">1861290000</a>
Type	SAIE-M8R-4-0.5U-FP-M8
GTIN (EAN)	4032248419364
Qty.	1 pc(s).

## SAIE-M8R-4-0.5U-FP-M8

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Net weight	14 g
------------	------

## Technical data customisable plug-in connectors

Cable glands	M 8	Contact surface	Gold-plated
Housing main material	Brass, nickel-plated	Number of poles	4
Plugging cycles	≥ 100	Protection degree	IP67, when screwed in
Rated current	4 A	Rated voltage	30 V
Temperature range of housing	-30...+90 °C	Type of connection	Pin

## General data

Cable glands	M 8	Cable length	0.5 m
Conductor O.D.	-	Connection thread	M8 snap
Contact surface	Gold-plated	Core cross-section	0.25 mm <sup>2</sup>
Housing main material	Brass, nickel-plated	Material	PVC
Mounting thread	M8	Number of poles	4
Plugging cycles	≥ 100	Protection degree	IP67, when screwed in
Rated current	4 A	Rated voltage	30 V
Rated voltage	60 V (3-pole) / 30 V (4-pole)	Strand / cable length	0.5 m
Temperature range of housing	-30...+90 °C	Type of connection	Pin

## Classifications

ETIM 6.0	EC002635	ETIM 7.0	EC003570
ETIM 8.0	EC003570	ETIM 9.0	EC003570
ECLASS 9.0	27-44-01-03	ECLASS 9.1	27-44-01-03
ECLASS 10.0	27-44-01-03	ECLASS 11.0	27-44-01-03
ECLASS 12.0	27-44-01-03	ECLASS 13.0	27-44-01-03

## Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	ebf89fc8-a87f-4691-b87a-dfb9921774b4

## Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E307231

## Downloads

Engineering Data	<a href="#">CAD data – STEP</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	<a href="#">FL FIELDWIRING EN</a> <a href="#">FL FIELDWIRING EN</a>


## SAIE-M8R-4-0.5U-FP-M8

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

# Drawings

## Wiring diagram



## Pole scheme

