

**IE-PP-V05M****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

For protecting your devices against dust and dirt.

**General ordering data**

|            |  |
|------------|--|
| Version    | Flange-mounted housing, protective cap |
| Order No.  | <a href="#">1968920000</a>             |
| Type       | IE-PP-V05M                             |
| GTIN (EAN) | 4032248692668                          |
| Qty.       | 1 pc(s).                               |

**IE-PP-V05M****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

|            |          |                |           |
|------------|----------|----------------|-----------|
| Depth      | 31 mm    | Depth (inches) | 1.22 inch |
| Net weight | 28.842 g |                |           |

**Temperatures**

|                       |             |
|-----------------------|-------------|
| Operating temperature | -40 °C...70 |
|-----------------------|-------------|

**General data**

|                   |      |                       |                   |
|-------------------|------|-----------------------|-------------------|
| Colour            | grey | Housing main material | diecast aluminium |
| Protection degree | IP67 |                       |                   |

**General standards**

|                         |         |
|-------------------------|---------|
| Certificate no. (cULus) | E316369 |
|-------------------------|---------|

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC002314    | ETIM 7.0    | EC002314    |
| ETIM 8.0    | EC002314    | ETIM 9.0    | EC002314    |
| ECLASS 9.0  | 27-44-02-08 | ECLASS 9.1  | 27-44-02-08 |
| ECLASS 10.0 | 27-44-02-08 | ECLASS 11.0 | 27-44-02-08 |
| ECLASS 12.0 | 27-44-02-08 | ECLASS 13.0 | 27-44-02-08 |

**Environmental Product Compliance**

|            |                                      |
|------------|--------------------------------------|
| REACH SVHC | Lead 7439-92-1                       |
| SCIP       | 67cf1078-beca-4687-860b-dc475a6ec24a |

**Approvals**

Approvals



|                         |            |
|-------------------------|------------|
| ROHS                    | Conform    |
| UL File Number Search   | UL Website |
| Certificate no. (cULus) | E316369    |

**Downloads**

|                    |  |
|--------------------|--|
| User Documentation | <a href="#">MAN IE GUIDE DE</a><br><a href="#">MAN IE GUIDE EN</a>   |
| Catalogues         | <a href="#">Catalogues in PDF-format</a>   |
| Brochures          | <a href="#">FL FIELDWIRING EN</a><br><a href="#">PI PROFINET CABLING EN</a><br><a href="#">FL FIELDWIRING EN</a><br><a href="#">PI PROFINET CABLING EN</a> |