

**SAI-SCREWTY TOOL BOX****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**The ideal tool for any application**

Screwty® is the ideal, all-purpose tool for tightening all common sensor and actuator cables. Even difficult-to-reach round plugs are accessible using the Screwty®. A simple turning movement tightens and loosens the connectors without the need for excessive force. The Screwty® is a unique and global solution since it fits with most cables and plugs from other vendors (over 90 %). The Screwty® consists of a handle with a conventional 1/4" adapter. Thus it can be used for all sizes: for M12 and M8 round plug-in connectors, and for M12F and M8F customisable plugs and sockets, as well as for all M23 plugs and sockets.

**General ordering data**

Version	Bolting tool
Order No.	<a href="#">1939170000</a>
Type	SAI-SCREWTY TOOL BOX
GTIN (EAN)	4032248615490
Qty.	1 pc(s).
Packaging	Plastic case + form insert

## SAI-SCREWTY TOOL BOX

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Net weight	1,320 g
------------	---------

## Screwing tools

Torque setting, max.	7 Nm	Torque setting, min.	0.5 Nm
----------------------	------	----------------------	--------

## Classifications

ETIM 6.0	EC000149	ETIM 7.0	EC000149
ETIM 8.0	EC000149	ETIM 9.0	EC000149
ECLASS 9.0	21-04-50-03	ECLASS 9.1	21-01-90-90
ECLASS 10.0	21-04-50-03	ECLASS 11.0	21-01-90-90
ECLASS 12.0	21-01-90-90	ECLASS 13.0	21-01-90-90

## Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

## Important note

Product information	<p>Included in delivery:</p> <ul style="list-style-type: none"> <li>• Torque screwdriver 0.5-1.7 Nm + Setting aid</li> <li>• Torque screwdriver 2.0-7.0 Nm</li> <li>• Interchangeable blade 1/4 inch</li> <li>• Attachment M8 for moulded lines</li> <li>• Attachment M8F for customisable connectors</li> <li>• Attachment M12 for moulded lines</li> <li>• Attachment M12F for customisable connectors</li> <li>• Blade set: <ul style="list-style-type: none"> <li>Torx T8 / T10 / T20 / T25</li> <li>Allen key 2.5 / 3.0 / 4.0</li> <li>Crosshead PH0 / PH1 / PH2</li> <li>Slotted 0.5x3.0 / 0.6x3.5 / 0.8x4.0</li> </ul> </li> <li>• Plastic Case + Form insert</li> </ul>
---------------------	---

## Downloads

Product Change Notification	<a href="#">20210319 Technical change to Screwty® torque screwdriver</a> <a href="#">20210319 Technische Änderung zu Screwty® Drehmomentschraubendreher</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	<a href="#">FL FIELDWIRING EN</a> <a href="#">FL FIELDWIRING EN</a>