

**ZQV 6N/4****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image**

The plug-in cross-connections feature easy handling and quick installation. This saves a great deal of time during installation in comparison with screwed solutions.

**General ordering data**

Version	Cross-connector (terminal), Plugged, Number of poles: 4, Pitch in mm (P): 8.00, Insulated: Yes, 41 A, orange
Order No.	<a href="#">1985780000</a>
Type	ZQV 6N/4
GTIN (EAN)	4050118370287
Qty.	60 pc(s).

**ZQV 6N/4****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Depth	3.1 mm	Depth (inches)	0.122 inch
Height	34.11 mm	Height (inches)	1.343 inch
Width	29.9 mm	Width (inches)	1.177 inch
Net weight	4.91 g		

**Temperatures**

Storage temperature	-25 °C...55 °C
---------------------	----------------

**Material data**

Material	Wemid	Colour	orange
UL 94 flammability rating	V-0		

**Additional technical data**

Explosion-tested version	Yes	Type of fixing	Plugged
--------------------------	-----	----------------	---------

**Cross-connector**

Number of cross-connected terminals	4	Rated current, 2-pole	41 A
Rated current, multi-pole	41 A	Type	Cross-connector

**Dimensions**

Pitch in mm (P)	8 mm
-----------------	------

**General**

Number of poles	4
-----------------	---

**Rating data**

Rated current	41 A
---------------	------

**Classifications**

ETIM 6.0	EC000489	ETIM 7.0	EC000489
ETIM 8.0	EC000489	ETIM 9.0	EC000489
ECLASS 9.0	27-14-11-40	ECLASS 9.1	27-14-11-40
ECLASS 10.0	27-14-11-40	ECLASS 11.0	27-14-11-40
ECLASS 12.0	27-14-11-40	ECLASS 13.0	27-25-03-03

**Important note**

Product information	Due to stability and temperature reasons It is only possible to break out 60% of contact elements The usage of cross connectors reduces the rated voltage to 400VThe voltage reduced to 25V if cut cross connection with blank cut edges are used
---------------------	---

**Approvals**

ROHS	Conform
------	---------

## ZQV 6N/4

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Downloads

Approval/Certificate/Document of Con-  
formity

[Confirmation of Standards EN 45545-2\\_2020-10](#)

Engineering Data

[CAD data – STEP](#)

Engineering Data

[Zuken E3.S](#)

User Documentation

[2434520000\\_BED-ANL\\_ZQV\\_A\\_REIHE.pdf](#)

[StorageConditionsTerminalBlocks](#)

[User Manual ZQV 2.5](#)

Catalogues

[Catalogues in PDF-format](#)

Brochures