

**IE-PS-V01M-2SC-POF****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Bayonet plug-in connector sets according to IEC  
61076-3-106 ver.1 (Ethernet/IP), RJ45 metal insert incl.  
SC insert

**General ordering data**

Version	FO connector, Version 1, SC-RJ POF, IP67
Order No.	<a href="#">1963280000</a>
Type	IE-PS-V01M-2SC-POF
GTIN (EAN)	4032248651757
Qty.	10 pc(s).



**IE-PS-V01M-2SC-POF****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

Depth	87 mm	Depth (inches)	3.425 inch
Height	30 mm	Height (inches)	1.181 inch
Width	30 mm	Width (inches)	1.181 inch
Net weight	125.5 g		

**Temperatures**

Operating temperature	-40 °C...70 °C
-----------------------	----------------

**General data**

Colour	Miscellaneous	Connection 1	SCRJ
Connection 2	Rapid connection system: crimping, cutting	Description of article	Version 1, SC-RJ POF
Fibre type	POF	Housing main material	Zinc diecast
Housing material, insert	PA, Zinc diecast	Insertion loss	0.5 dB singlemode, 0.4 dB multimode, ≤ 1.0 dB POF
Plugging cycles	500	Protection degree	IP67
Return loss (attenuation)	40 dB singlemode; 30 dB multimode	Sheath diameter, max.	10 mm
Sheath diameter, min.	5 mm		

**General standards**

Connector standard	IEC 61076-3-106 Var. 1, IEC 61754-24
--------------------	---

**Classifications**

ETIM 6.0	EC001122	ETIM 7.0	EC001122
ETIM 8.0	EC001122	ETIM 9.0	EC001122
ECLASS 9.0	19-17-01-22	ECLASS 9.1	19-17-01-22
ECLASS 10.0	19-17-01-22	ECLASS 11.0	19-17-01-22
ECLASS 12.0	19-17-01-22	ECLASS 13.0	19-17-01-22

**Environmental Product Compliance**

REACH SVHC	Lead 7439-92-1 6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol 119-47-1
SCIP	e5bbf197-73b5-420b-90c0-0173b7b3b6b7

**Approvals**

ROHS	Conform
------	---------

**Downloads**

Approval/Certificate/Document of Conformity	<a href="#">GOST Approval</a>
User Documentation	<a href="#">MAN IE GUIDE DE</a> <a href="#">MAN IE GUIDE EN</a> <a href="#">Designation key / Type key</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	<a href="#">FL FIELDWIRING EN</a> <a href="#">PI PROFINET CABLING EN</a>




## IE-PS-V01M-2SC-POF

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

# Drawings

## Dimensioned drawing





**IE-PS-V01M-2SC-POF****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****LWL-SC**

FO SC inserts for plug-in connectors ver.1 / 4 / 14

**General ordering data**

Type	IE-SCRJ-IP67-POF-100	Version
Order No.	<a href="#">1278430000</a>	FO connector, Replacement crimp barrel, IP67 with housing
GTIN (EAN)	4050118069136	
Qty.	100 pc(s).	

**Dust caps**

For protecting your devices against dust and dirt.

**General ordering data**

Type	IE-PP-V01P	Version
Order No.	<a href="#">1965690000</a>	Plug housing protective cap
GTIN (EAN)	4032248653911	
Qty.	10 pc(s).	



**IE-PS-V01M-2SC-POF****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****Blank**

ESG is the tried-and-tested marker in MultiCard format for use on many well-known electrical devices. The result is high-quality device marking with a high-contrast appearance.

Various types are available for devices from manufacturers like Siemens, ABB, Beckhoff etc.

Advantages at a glance:

- Tags for universal usage, self-adhesive or clip-on tags, depending on type
- For aligned equipment, e.g. circuit breakers, we supply ESG markers for clipping onto tag rails
- Individual laser-quality printing according to specifications

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

**General ordering data**

Type	ESG 9/11 K MC NE WS	Version
Order No.	<a href="#">1857440000</a>	ESG, Device markers x 11 mm, PA 66, Colour: white, Self-adhesive
GTIN (EAN)	4032248402731	
Qty.	200 pc(s).	

**Crimp Sets**

Crimp sets

**General ordering data**

Type	TOOL SET IE-POF	Version
Order No.	<a href="#">1208930000</a>	Crimping tool: HTX-IE-POF, Stripping tool: Multi-Stripax IE-POF
GTIN (EAN)	4032248990283	
Qty.	1 pc(s).	