

**HDC CM BUS SV GCA F****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

The ConCept-CSB module is a double module and takes up two slots in the ConCept module frame. The ConCept-CSB module consists of a module carrier that is capable of holding two contact carriers. The contact carrier is manufactured with a die-cast zinc alloy which provides it with excellent shielding capabilities. The crimp contacts are insulated from the contact carrier and mounted in a plastic insert. A variety of pole counts – 1, 4 and 8 poles – are available to ensure compatibility with a wide range of applications.

**General ordering data**

Version	Heavy-duty connectors, HDC insert, ConCept module
Order No.	<a href="#">1983820000</a>
Type	HDC CM BUS SV GCA F
GTIN (EAN)	403224868895 1
Qty.	1 pc(s).

## HDC CM BUS SV GCA F

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Height	3.9 mm	Height (inches)	0.154 inch
Width	21.5 mm	Width (inches)	0.846 inch
Length	33.5 mm	Length (inches)	1.319 inch
Net weight	8.8 g		

## Temperatures

Limit temperature	-40 °C ... 70 °C
-------------------	------------------

## ConCept Pneumatic module

Colour	Silver grey	UL 94 flammability rating	V-0
--------	-------------	---------------------------	-----

## Dimensions

Height of socket	3.9 mm	Total length base	33.5 mm
Width	21.5 mm		

## General data

Colour	Silver grey	Free from halogens	false
Low smoke acc. DIN EN 45545-2	Yes	Material	Polycarbonate
Plugging cycles	≥ 500	Series	ConCept module
Type	Earth connection clamp	UL 94 flammability rating	V-0

## Version

Material	Polycarbonate
----------	---------------

## Classifications

ETIM 6.0	EC002312	ETIM 7.0	EC002312
ETIM 8.0	EC002312	ETIM 9.0	EC002312
ECLASS 9.0	27-44-02-92	ECLASS 9.1	27-44-02-18
ECLASS 10.0	27-44-02-92	ECLASS 11.0	27-44-02-92
ECLASS 12.0	27-44-02-92	ECLASS 13.0	27-44-02-92

## Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (cURus)	E92202

## Downloads

Engineering Data	<a href="#">CAD data – STEP</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	<a href="#">FL FIELDWIRING EN</a>