

DMS PRO ZERT**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Only for Europe



Weidmüller torque screwdrivers have an ergonomic design and are therefore ideal for use with one hand. They can be used without causing fatigue in all installation positions. Apart from that, they incorporate an automatic torque limiter and have a good reproducibility accuracy.

General ordering data

Version	Mounting tool
Order No.	1987840000
Type	DMS PRO ZERT
GTIN (EAN)	4050118372359
Qty.	1 pc(s).

DMS PRO ZERT**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Width	276 mm	Width (inches)	10.866 inch
Net weight	480 g		

Technical data

Description of article	Mains-operated torque screwdriver with 1/4" drive
------------------------	---

Electric screwdriver

Rechargeable batteries	Li-Ion battery	Torque setting, max.	3 Nm
Torque setting, min.	0.36 Nm	Weight	500 g

Screwing tools

Torque setting, max.	3 Nm	Torque setting, min.	0.36 Nm
----------------------	------	----------------------	---------

Classifications

ETIM 6.0	EC001395	ETIM 7.0	EC001395
ETIM 8.0	EC001395	ETIM 9.0	EC001395
ECLASS 9.0	21-05-21-90	ECLASS 9.1	21-04-04-17
ECLASS 10.0	21-05-21-90	ECLASS 11.0	21-05-08-90
ECLASS 12.0	21-05-08-90	ECLASS 13.0	21-05-08-90

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	8a39b146-a7e9-4fe1-a2bc-f82c0bb3aeeb

Approvals

Approvals



ROHS	Conform
------	---------

Downloads

Approval/Certificate/Document of Conformity	1987840000_DECLARATION_OF_CONFORMITY.pdf
User Documentation	Manual
Catalogues	Catalogues in PDF-format

DMS PRO ZERT

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings


Example of use



Example of use



Example of use



DMS PRO ZERT

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

E6.3 bits - Pozidriv / Supadriv



1/4" hexagon drive to DIN 3126, form E6.3 for direct machine connection
Crosshead bits Pozidriv PZ/DIN 5262, 1/4" drive, E 6.3 DIN 3126

General ordering data

Type	BIT E6,3 PZ2X70	Version
Order No.	9024110000	Accessories, Screwdriver insert
GTIN (EAN)	4008190870706	
Qty.	5 pc(s).	
Type	BIT E6,3 PZ1X70	Version
Order No.	9024100000	Accessories, Screwdriver insert
GTIN (EAN)	4008190870713	
Qty.	5 pc(s).	

E6.3 bits - Phillips / recess



1/4" hexagon drive to DIN 3126, form E6.3 for direct machine connection
Crosshead bits are Phillips-Recessed type PH/DIN 5260. 1/4" drive, E6.3 DIN 3126

General ordering data

Type	BIT E6,3 PH1X70	Version
Order No.	9024080000	Accessories, Screwdriver insert
GTIN (EAN)	4008190870744	
Qty.	5 pc(s).	
Type	BIT E6,3 PH2X70	Version
Order No.	9024090000	Accessories, Screwdriver insert
GTIN (EAN)	4008190870720	
Qty.	5 pc(s).	

DMS PRO ZERT

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Bit assortment, E6.3



1/4" hexagon drive to DIN 3126, form E6.3 for direct machine connection

General ordering data

Type	BIT-BOX WI DMS 3	Version
Order No.	9024970000	Accessories, Mounting tool
GTIN (EAN)	4032248068067	
Qty.	1 pc(s).	

DMS PRO



Weidmüller torque screwdrivers have an ergonomic design and are therefore ideal for use with one hand. They can be used without causing fatigue in all installation positions. Apart from that, they incorporate an automatic torque limiter and have a good reproducibility accuracy.

General ordering data

Type	LG DMS PRO/ DMS 3	Version
Order No.	9007460000	DMS 3, 90 % bei 3x 500 V AC / > 91 % bei 3 x 400 V AC
GTIN (EAN)	4008190404970	
Qty.	1 pc(s).	
Type	AKKU DMS PRO	Version
Order No.	1479110000	Mounting tool
GTIN (EAN)	4050118348712	
Qty.	1 pc(s).	
Type	DMS PRO SET	Version
Order No.	1479090000	Mounting tool
GTIN (EAN)	4050118286786	
Qty.	1 pc(s).	

DMS PRO ZERT

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

BE6.3 bits - slotted

1/4" hexagon drive to DIN 3126, form E6.3 for direct machine connection

Slot-head bits DIN 5264, 1/4" drive, E6.3 DIN 3126



General ordering data

Type	BIT E6,3 1,2X6,5X70	Version
Order No.	9202740000	Accessories, Screwdriver insert
GTIN (EAN)	4032248504718	
Qty.	5 pc(s).	
Type	BIT E6,3 1,0X5,5X70	Version
Order No.	9024040000	Accessories, Screwdriver insert
GTIN (EAN)	4008190852665	
Qty.	5 pc(s).	
Type	BIT E6,3 0,4X2,5X70	Version
Order No.	9202750000	Accessories, Screwdriver insert
GTIN (EAN)	4032248504725	
Qty.	5 pc(s).	
Type	BIT E6,3 0,6X3,5X70	Version
Order No.	9024020000	Accessories, Screwdriver insert
GTIN (EAN)	4008190852627	
Qty.	5 pc(s).	
Type	BIT E6,3 Z 0,8X4,0X39	Version
Order No.	9025590000	Accessories, Screwdriver insert
GTIN (EAN)	4008190151935	
Qty.	10 pc(s).	
Type	BIT E6,3 0,5X3,0X70	Version
Order No.	9024000000	Accessories, Screwdriver insert
GTIN (EAN)	4008190852634	
Qty.	5 pc(s).	
Type	BIT E6,3 0,8X4,0X70	Version
Order No.	9024030000	Accessories, Screwdriver insert
GTIN (EAN)	4008190852658	
Qty.	5 pc(s).	