

**IE-USB-A-A-1.5M****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Assembled IE cables

**General ordering data**

Version	USB cable, USB A, USB A, PVC, 1.5 m
Order No.	<a href="#">1993550015</a>
Type	IE-USB-A-A-1.5M
GTIN (EAN)	4050118378573
Qty.	1 pc(s).

**IE-USB-A-A-1.5M****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

Length	1.5 m	Length (inches)	59.055 inch
Net weight	52 g		

**Temperatures**

Operating temperature	-15 °C...80
-----------------------	-------------

**Technical specifications for cable**

Sheathing colour	black
------------------	-------

**General technical data**

Contact surface	Gold over nickel
-----------------	------------------

**Cable structure**

Cross-section	2*AWG28 + 2*AWG24	Material sheath	PVC
Sheath diameter	4.5 mm	Sheath diameter, max.	4.7 mm
Sheath diameter, min.	4.3 mm	Sheathing colour	black

**Plug**

Plug left	USB A, IP20, male contact, straight, plug, Plastic, shielded	Plug right	USB A, IP20, male contact, straight, plug, Plastic, shielded
-----------	--	------------	--

**Plug, left**

Contact surface, plug, left	Gold over nickel	Plug left	USB A, IP20, male contact, straight, plug, Plastic, shielded
-----------------------------	------------------	-----------	--

**Plug, right**

Contact surface	Gold over nickel	Plug right	USB A, IP20, male contact, straight, plug, Plastic, shielded
-----------------	------------------	------------	--

**Classifications**

ETIM 6.0	EC001408	ETIM 7.0	EC001408
ETIM 8.0	EC001408	ETIM 9.0	EC001408
ECLASS 9.0	27-06-20-11	ECLASS 9.1	27-06-90-90
ECLASS 10.0	27-06-01-06	ECLASS 11.0	27-06-01-06
ECLASS 12.0	27-06-01-06	ECLASS 13.0	27-06-01-06

**Approvals**

ROHS	Conform
------	---------

## IE-USB-A-A-1.5M

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Downloads

User Documentation	<a href="#">MAN IE GUIDE DE</a> <a href="#">MAN IE GUIDE EN</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	<a href="#">FL FIELDWIRING EN</a> <a href="#">PI PROFINET CABLING EN</a> <a href="#">PI PROFINET CABLING EN</a>