

CRIMPFIX E**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

- For automatic stripping and crimping
- Time-saving and efficient processing
- Easily adjustable to the respective cross-section range
- Stripping and crimping in one work step
- The processing of sleeves or contacts from other manufacturers can cause machine failures and defects!

General ordering data

Version	Automatic stripper and crimper, 0.5mm ² , 2.5mm ²
Order No.	2439140000
Type	CRIMPFIX E
GTIN (EAN)	4050118451917
Qty.	1 pc(s).
Delivery status	This article will no longer be available in the future.
Available until	2025-01-06
Alternative product	2833890000

CRIMPFIX E**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Depth	349 mm	Depth (inches)	13.74 inch
Height	230 mm	Height (inches)	9.055 inch
Width	288 mm	Width (inches)	11.339 inch
Net weight	14,000 g		

PW65 maintenance - automatic stripping/crimping

Consumables	Linked wire-end ferrules, with plastic collar	Crimping	Trapezoidal
Crimping length	8 mm	Crimping range, max.	2.5 mm ²
Crimping range, min.	0.5 mm ²	Drive	Electro-mechanical
Electrical connection	100-240 V / 50/60 Hz / 100 VA	Length of wire-end ferrule	14 mm
Pulse time	approx. 1.8 sec	Stripping range	0.5 - 2.5 mm ² (~AWG 20-14)
Wire end ferrules cross-section, max.	2.5 mm ²	Wire end ferrules cross-section, min.	0.5 mm ²

Classifications

ETIM 6.0	EC002778	ETIM 7.0	EC002778
ETIM 8.0	EC002778	ETIM 9.0	EC002778
ECLASS 9.0	17-13-01-01	ECLASS 9.1	17-13-01-01
ECLASS 10.0	17-13-01-01	ECLASS 11.0	17-13-01-01
ECLASS 12.0	17-13-01-01	ECLASS 13.0	17-13-01-01

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	d2df479e-2b79-4e98-adc7-b03577df98ae

Approvals

Approvals



ROHS	Conform
------	---------

Downloads

User Documentation	Manual
Catalogues	Catalogues in PDF-format

CRIMPFIX E

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Drawings



CRIMPFIX E**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Accessories / replacement parts**

- For automatic stripping and crimping
- Time-saving and efficient processing
- Easily adjustable to the respective cross-section range
- Stripping and crimping in one work step
- The processing of sleeves or contacts from other manufacturers can cause machine failures and defects!

General ordering data

Type	HAKL/TPKL CF2.5M/CF2.5	Version
Order No.	9205810000	Accessories, Replacement part
GTIN (EAN)	4032248814008	
Qty.	1 pc(s).	
Type	AIMESA CF U/LS TIN	Version
Order No.	1132150000	Automatic machines, Replacement part
GTIN (EAN)	4032248920082	
Qty.	1 pc(s).	